



<b>OVERVIEW</b>	
UPC Code	037332284020
Brand Compatibility	Juniper
Technology	Fiber; Multimode
Optical Mode	OM4
Mode Type	Multimode
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	0.70 x 3.10 x 5.70
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.700 x 3.100 x 5.700
Unit Weight (lbs.)	0.1102
Unit Weight (kg)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Maximum Data Rate	10 Gbps
Network Compatibility	10 Gbps
Wavelength	840nm; 850nm; 860nm
Transmission Distance	400 m
<b>CONNECTIONS</b>	
Side A - Connector 1	SFP+ (FEMALE)
Side B - Connector 1	LC DUPLEX (MALE)
Connector Material	Zinc Alloy
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	10 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Driver Required	No
Optical Port	LC

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; IEC/EN 63000
Product Compliance	RoHS; CE (Europe); FCC Part 15 Class B (USA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.