

Fiber Optic Mode Conditioning Patch Cable (SC/SC), 3M (9.84 ft.)

MODEL NUMBER: N426-03M



Highlights

- 3 Meter SC/SC Mode Conditioning Cable
- 62.5/125 and 8.3/125
- Run 1000Base-LX Gigabit Ethernet over MMF by offsetting signal loss
- IEEE 802.3z Gigabit Ethernet Compliant

Package Includes

- 3 Meter SC/SC Mode Conditioning Cable

Features

- Use Singlemode Transceivers on Multimode Fiber Backbones
- 62.5/125 and 8.3/125
- Offsets the Singlemode Laser launch from the center of a Multimode fiber
- Available in a variety of connector combinations

Specifications

OVERVIEW	
UPC Code	037332127297
Clad Diameter	125 micron; 125 micorn
Core Diameter	62.5 micron; 8.3 micron
Number of Fibers	2
Technology	Mode Conditioning
INPUT	
Cable Length (ft.)	9.8
Cable Length (m)	3
Cable Length (in.)	118.1
PHYSICAL	
Cable Jacket Rating	LSZH



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Orange; Yellow
Shipping Dimensions (hwd / cm)	0.64 x 14.48 x 15.49
Shipping Dimensions (hwd / in.)	0.25 x 5.70 x 6.10
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
CONNECTIONS	
Side A - Connector 1	SC DUPLEX (MALE)
Side B - Connector 1	SC DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>