

Juniper-Compatible QSFP-40GBASE-SR4 QSFP+ Transceiver - 40GBase-SR4, MTP/MPO MMF, 40 Gbps, 850 nm, 400 m (1312 ft.)

MODEL NUMBER: N286-40G-ESR4-J



Connects a multimode Gigabit Ethernet fiber optic network cable to a Juniper switch or server's QSFP+ port.

Features

QSFP+ Transceiver for Connecting to Your Juniper Network Switch or Server

This QSFP+ transceiver allows you to connect a multimode fiber optic cable to a 40 Gbps network router, server or switch. It transmits data up to 400 meters (1312 feet) using an 850 nm wavelength. The zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

Functionally Equivalent to Juniper QSFP-40GBASE-SR4 Transceiver Module

The MSA-compliant N286-40G-ESR4-J functions just like the equivalent Juniper QSFP-40GBASE-SR4 transceiver module and is manufactured to meet or exceed Juniper specifications. You can use this transceiver with any compatible Juniper router, server or switch and receive the same performance as the QSFP-40GBASE-SR4.

Hot-Swappable for Installation Without Network Interruption

This input/output device is fully hot-swappable, so you can install it without a potentially costly 40 Gbps network shutdown or device reboot. Just plug the QSFP+ end of the transceiver into your Juniper network device. The other end has an MTP/MPO connector to link with multimode fiber optic cable (sold separately). A push/pull tab connector is easily accessible in high-density data center applications and makes the plug-and-play transceiver easy to install and remove with one hand.

Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring

DDM support lets you keep track of operating information in real time, such as transceiver temperature, input and output power and supply voltage.

Highlights

- QSFP+ transceiver module 100% compatible with Juniper's QSFP-40GBASE-SR4 module
- Provides 40 Gbps throughput up to 400 m via multimode fiber cabling
- 12-strand MTP/MPO connector supports 40GBase-SR4 signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

Package Includes

N286-40G-ESR4-J QSFP+ Transceiver

Specifications

OVERVIEW	
UPC Code	037332284075
Brand Compatibility	Juniper



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	Fiber; Multimode
Optical Mode	OM4
Mode Type	Multimode
CONNECTIONS	
Side A - Connector 1	QSFP+ (MALE)
Side B - Connector 1	12-STRAND MTP/MPO (MALE)
Connector Material	Zinc Alloy
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.70 x 3.10 x 5.70
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.700 x 3.100 x 5.700
Unit Weight (lbs.)	0.1102
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 95% RH, Non-Condensing
COMMUNICATIONS	
Maximum Data Rate	40 Gbps
Network Compatibility	40 Gbps
Wavelength	840nm; 860nm
Transmission Distance	400 m
FEATURES & SPECIFICATIONS	
Data Transfer Rate	40 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Driver Required	No
Optical Port	MPO/MTP
STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; IEC/EN 63000
Product Compliance	RoHS; CE (Europe); FCC Part 15 Class B (USA); UKCA
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.