

## Industrial Gigabit SFP Transceiver - 1000Base-LX, Singlemode, LC Duplex, DDM, -40° to 85°C, 10 km (6.2 mi.)

MODEL NUMBER: N286I-1P25GLXD1



Industrial transceiver module links a Gigabit Ethernet network fiber cable to the SFP port on a switch, firewall or other network device.

### Features

#### Industrial-Grade SFP Transceiver Module Connects Fiber Cabling to Your Network Device

Tripp Lite's N286I-1P25GLXD1 provides 1000Base-LX throughput over singlemode fiber cable up to 10 kilometers (6.2 miles) at 1310 nm. It complies with IEEE 802.3z 1000Base-LX standards, supports Digital Diagnostic Monitoring (DDM) and transmits bi-directional data at speeds up to 1.25 Gbps. Connect the transceiver to any standard SFP slot on an industrial switch or fiber converter, such as Tripp Lite's NGI-Series Industrial Gigabit Ethernet Switches.

#### Built to Last in Harsh Industrial Environments

The N286I-1P25GLXD1 adds 10/100/1000 Mbps Gigabit Ethernet connectivity to your industrial application, such as factory automation, rail and intelligent transportation systems (ITSs), marine, oil and gas, mining and other environments with wide temperature ranges. The high-strength housing withstands vibration, shock and free fall. It can also operate in extreme temperatures ranging from -40 to 85 degrees Celsius (-40 to 185 degrees Fahrenheit).

#### Hot-Pluggable for Installation Without Network Interruption

This transceiver module is fully hot-pluggable, so you can install it without a potentially costly network shutdown or device reboot. Just plug the SFP end of the transceiver into your network device. The other end has an LC duplex connector to link with high-speed fiber cable (sold separately). A convenient bail clasp latch helps you carefully remove the module from the device.

## Specifications

OVERVIEW	
UPC Code	037332268334
Product Type	Industrial Gigabit SFP Transceiver

### Highlights

- Ideal for harsh environments, including factories, oil and gas, mines and rail systems
- Provides 1000Base-LX throughput up to 10 km via singlemode fiber cabling
- Hot-swappable interface lets you install and uninstall without shutting down
- Industrial-grade transceiver supports operating temperature range of -40° to 85°C
- Supports bi-directional Gigabit Ethernet data transfer rates up to 1.25 Gbps

### System Requirements

Works with standard SFP slots found on industrial switches and fiber converters, such as Tripp Lite's NGI Series

### Package Includes

N286I-1P25GLXD1 Industrial Gigabit SFP Transceiver



Brand Compatibility	TRENDnet
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	0.43 x 0.55 x 2.64
Unit Weight (lbs.)	0.0377
Unit Weight (kg)	0.02
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-40°F-185°F (-40°C~85°C)
Relative Humidity	5% ~ 95%
Operating Temperature	-40°F-185°F (-40°C~85°C)
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit)
Wavelength	1310nm
Transmission Distance	10Km
<b>CONNECTIONS</b>	
Side A - Connector 1	SFP (MALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	1 Gbps
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	IEEE Standard: IEEE 802.3z 1000Base-LX
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>