

**Important Note**

Guaranteed compatibility when used with recommended cabling. Designed specifically for use with N846-Series cables.

**100Gb/120Gb Pass-Through Cassette - (x12) 24-Fiber MTP/MPO ( Female )**

MODEL NUMBER: **N484-12M24**



**Description**

The N484-12M24 is a high-density 100/120 Gb Pass-Through Cassette with (x12) 24-Fiber MTP/MPO connections. Designed specifically for use with N484-00U and N484-01U chassis. Up to four cassettes per N484-01U or one cassette per N484-00U. Guaranteed compatibility when used with recommended cabling. Designed specifically for use with N846-Series cables. Installation is simple, with the cassette being easily installed or removed using screw tabs to lock or unlock it from the panel; no tools required. Furthermore, each cassette features factory-terminated connectors that reduce the time and labor required of field connector terminations. Cassette housing made with heavy-duty 1.0mm cold-rolled steel.

**Features**

- High Density Fiber Cassette for use with N484-00U and N484-01U chassis'
- 100/120Gb Pass-through Cassette, with (x12) 24-Fiber MTP/MPO connections
- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with N846-Series cables
- Installation is simple, with the cassette being easily installed or removed using screw tabs to lock or unlock it from the panel; no tools required
- Factory terminated connectors reduce the time and labor required of field connector terminations
- Housing made of heavy duty, 1.0mm Cold Rolled Steel
- Includes dust caps for unused ports

**Highlights**

- High Density Fiber Cassette for use with N484-00U and N484-01U chassis'
- 100/120Gb Pass-through Cassette, with (x12) 24-Fiber MTP/MPO connections
- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with cables, such as the N846-Series cables
- Factory terminated connectors reduce the time and labor required of field connector terminations

**System Requirements**

- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with N846-Series cables

**Package Includes**

- N484-12M24 100/120GbE Pass-Through Cassette - (x12) 24-Fiber MTP/MPO ( Female )
- Quick Start Guide

**Specifications**

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332187208 |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                             |
|-------------------------------------|-----------------------------|
| Technology                          | Fiber                       |
| <b>CONNECTIONS</b>                  |                             |
| Number of Ports                     | 12                          |
| Side A - Connector 1                | 24-STRAND MTP/MPO (FEMALE)  |
| Side B - Connector 1                | 24-STRAND MTP/MPO (FEMALE)  |
| <b>PHYSICAL</b>                     |                             |
| Color                               | Black                       |
| Shipping Dimensions (hwd / in.)     | 2.36 x 5.12 x 1.46          |
| Shipping Dimensions (hwd / cm)      | 5.99 x 13.00 x 3.71         |
| Shipping Weight (lbs.)              | 0.49                        |
| Shipping Weight (kg)                | 0.22                        |
| Unit Dimensions (hwd / in.)         | 1.200 x 3.500 x 4.700       |
| Unit Weight (lbs.)                  | 0.3                         |
| Unit Weight (kg)                    | 0.14                        |
| <b>ENVIRONMENTAL</b>                |                             |
| Operating Temperature Range         | -4° to 122°F (-20° to 50°C) |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                             |
| Product Compliance                  | RoHS; REACH                 |
| <b>WARRANTY &amp; SUPPORT</b>       |                             |
| Product Warranty Period (Worldwide) | Lifetime limited warranty   |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.