

Preloaded Fiber Panel, 1U - 8x LC/LC Duplex Cables (M/M), OS2 Singlemode, 10 m (32.8 ft.)

MODEL NUMBER: N48S-8L2L-10



1U panel comes preloaded with spools of singlemode fiber cable that allow you to extend the exact length required and store the excess out of sight.

Description

Preloaded Fiber Panel, 1U - 8x LC/LC Duplex Cables (M/M), OS2 Singlemode, 10 m (32.8 ft.)

Features

1U Panel Solution Comes with Cabling Preloaded to Cut Costs and Save Time

All necessary cabling is included with this preloaded fiber panel, coiled inside and ready for immediate use. The aluminum 1U chassis features eight LC Duplex singlemode cables, all 10 meters (32.8 feet) in length to make management easy. The panel opens to provide easy access to stored cables. Use only as much cabling as you need. The remainder stores inside the chassis to eliminate cable clutter, allow better airflow through the rack and make equipment maintenance and replacement easier. The cables and panels have labels to help with organization. You also avoid the expense and effort of custom cabling. The flexibility in cable length lets you reuse the cables if equipment is moved. The N48S-8L2L-10 mounts in just 1U of space in an EIA-standard 19-inch rack.

Specifications

OVERVIEW	
UPC Code	037332262370
Product Type	Preloaded
Technology	Singlemode
Optical Mode	OS2; SM
Panel Dimensions	17.32" X 1.73" X 10.20"
Panel Cable Number	8
Panel Cable Length (m)	10

Highlights

- 8 LC Duplex 10-meter OS2 singlemode cables come coiled inside for instant use
- Use only as much cable as you need; store the remainder inside to avoid clutter
- Flexible cable length allows reuse of cables if equipment is moved
- Aluminum chassis mounts into 1U of space in EIA-standard 19 in. racks

Applications

- Save the expense and effort of buying custom cables or repurchasing cables after moving rack equipment
- Eliminate cable clutter by using only as much as you need and storing excess cable inside the panel

Package Includes

- N48S-8L2L-10 Preloaded Fiber Panel
- (8) LC Duplex to LC Duplex cables, 10 m (32.8 ft.)
- Installation guide



Mode Type	Singlemode
Firmware / Software Docs	
Offset Ports	No
PHYSICAL	
Primary Form Factor	Rackmount
Cable Jacket Color	Yellow
Cable Jacket Material	PVC
Cable Jacket Rating	OFNP
Cable Outer Diameter (OD)	2.9MM
Clad Diameter (microns)	125
Core Diameter (microns)	9
Primary Coating Diameter (microns)	245
Number of Fibers	2
Cable Length (ft.)	32.8
Cable Length (m)	10.00
Cable Length (in.)	393.7
Minimum Bend Radius	20MM (DYNAMIC); 10MM (STATIC)
Rack Height	1U
Shipping Dimensions (hwd / in.)	4.30 x 22.80 x 18.90
Shipping Weight (kg)	3.50
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (-20 TO 60 C)
Storage Temperature Range	-4 TO 140 F (-20 TO 60 C)
Operating Humidity Range	5% TO 85% RH, NON-CONDENSING
Storage Humidity Range	5% TO 85% RH, NON-CONDENSING
COMMUNICATIONS	
Network Compatibility	10 Gbps; 40 Gbps; 100 Gbps; 400 Gbps
Wavelength	1310nm; 1550nm
Attenuation @ 1310NM	0.36 dB/KM
Attenuation @ 1550NM	0.22 dB/KM
Insertion Loss	0.30dB
CONNECTIONS	



Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)
Endface Polish	UPC
Connector Color	Blue; White
FEATURES & SPECIFICATIONS	
All-in-One Kit	Yes
Built-in Cables	Yes
Optical Port	LC
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>