

## Duplex Multimode 62.5/125 Fiber Patch Cable (LC/ST), 10M (33 ft.)

MODEL NUMBER: **N318-10M**



### Highlights

- Premium 62.5/125 duplex (zipcord) fiber patch cable - 10 m
- Ideal for LAN applications
- Glass fiber composition
- LC/ST connectors

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/ST connectors

### Package Includes

- 10-meter duplex MMF LC/ST 62.5/125 fiber cable

### Description

Tripp Lite's 10-meter multimode duplex fiber optic LC/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC to ST connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 10-meters/Connectors: 2 LC/ST connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications where links are 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

| OVERVIEW         |              |
|------------------|--------------|
| UPC Code         | 037332122629 |
| Clad Diameter    | 125 micron   |
| Core Diameter    | 62.5 micron  |
| Number of Fibers | 2            |



|                                     |                           |
|-------------------------------------|---------------------------|
| Technology                          | Multimode                 |
| Optical Mode                        | OM1                       |
| <b>INPUT</b>                        |                           |
| Cable Length (ft.)                  | 32.8                      |
| Cable Length (m)                    | 10                        |
| Cable Length (in.)                  | 393.7                     |
| <b>PHYSICAL</b>                     |                           |
| Color                               | Orange                    |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.90      |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.75        |
| Shipping Weight (kg)                | 0.06                      |
| Shipping Weight (lbs.)              | 0.13                      |
| <b>COMMUNICATIONS</b>               |                           |
| Network Speed                       | 1Gbps                     |
| <b>CONNECTIONS</b>                  |                           |
| Side A - Connector 1                | LC DUPLEX (MALE)          |
| Side B - Connector 1                | ST DUPLEX (MALE)          |
| <b>SPECIAL FEATURES</b>             |                           |
| Push/Pull Tabs                      | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Certifications                      | ROHS                      |
| Approvals                           | FDDI and OFNR rated       |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>