


DC Power Supply for Tripp Lite N785-CH12 Media Converter Chassis, 75W

MODEL NUMBER: N785-CH75W-DC



75W DC power supply provides primary or redundant power to your media converter installation.

Features

Powers Your Tripp Lite N785-CH12 12-Port Media Converter Chassis

This 75-watt DC power supply works with the Tripp Lite N785-CH12 media converter chassis to provide primary or redundant power. The N785-CH12 comes with a pre-installed AC power supply, but you can swap it out for the N785-CH75W-DC if you prefer DC power. This DC power supply can be used with any DC power source up to 48V 3A. A second DC power supply is also recommended to provide redundant power that helps prevent unwanted and expensive downtime. **Note:** Only one type of power supply should be used with the N785-CH12. Do not mix DC and AC power supplies.

Specifications

OVERVIEW	
UPC Code	037332267078
Accessory Type	Power Supply
Accessory Class	Networking Accessories
POWER	
Power Source Type	AC Adapter
External Power Supply Plug(s)	NEMA 5-15P North America
External Power Supply Input Specs (V / Hz / A)	48V / 3A
External Power Supply Output Specs (V / A)	12V / 6.5A
External Power Supply Cord Length (ft.)	6

Highlights

- Supplies DC power to a media converter installation using Tripp Lite's N785-CH12
- Multiple power supplies provide primary and redundant power to prevent downtime

System Requirements

Tripp Lite N785-CH12 Media Converter Chassis

Package Includes

N785-CH75W-DC 75W DC Power Supply

External Power Supply Cord Length (m.)	1.83
PHYSICAL	
Power Cord Color	Black
Unit Dimensions (hwd / in.)	5.240 x 2.320 x 9.060
Unit Dimensions (hwd / cm)	13.3 x 5.9 x 23.0
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32 to 122F (0 to 50C)
Storage Temperature Range	14 to 158F (-10 to 70C)
Operating Humidity Range	10% to 90%
Storage Humidity Range	5% to 95%
FEATURES & SPECIFICATIONS	
Auto MDIX Support	No
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; RoHS
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty