


# 100G Duplex Singlemode 9/125 OS2 Armored Fiber Optic Cable (LC/LC Duplex M/M), LSZH, Yellow, 100 m (328 ft.)

MODEL NUMBER: N370-100M-AR



100 GbE Ethernet cable with protective steel armor supports high bandwidths necessary for cloud services, hyperscale data centers and telecom carriers.

## Features

### 100 GbE Cable Supports Higher Bandwidths Needed for Data Networking

As the amount of traffic in data networks grows, so does the need for devices and fiber cables to support higher bandwidths in cloud services, hyperscale data centers, telecom applications and equipment OEM companies. This duplex singlemode 9/125 OS2 cable is an ideal choice for 100G Ethernet applications up to 100 meters (328 feet) at 1310 nm. It is also backward compatible with 10 Gb, 25 Gb and 40 Gb networks, so you can future-proof your current application for an eventual upgrade to 100 Gb.

### Armored Cable Provides Great Flexibility and Durability

The N370-100M-AR can be run anywhere and does not need to be in conduit. Built-in flexible stainless steel and robust Aramid yarn protect the optical fibers more effectively than standard fiber optic cables do. The rugged armored tubing allows optical fiber to be installed in the most hazardous areas, including indoor environments with excessive dust, oil, gas and moisture. This fiber cable provides low insertion loss and high return loss.

### Yellow Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The OS2-rated cable has a yellow jacket to identify it as singlemode in a crowded patch panel or switch and prevent it from becoming accidentally disconnected. The round low-smoke zero-halogen (LSZH) jacket limits the amount of toxic smoke emitted in case of combustion, making it suitable for poorly ventilated areas.

## Specifications

OVERVIEW	
UPC Code	037332264343
Technology	Singlemode

## Highlights

- OS2-rated cable recommended for 100 Gb speeds up to 100 meters (@ 1310 nm)
- Flexible stainless steel tubing protects fiber and helps cable stand up to rigorous use
- Backward compatible with 10/25/40 Gb networks to facilitate future-proofing
- Yellow LSZH jacket allows fast, easy identification in a crowded switch or patch panel

## Applications

Connect 100G fiber Ethernet networks in your cloud service, hyperscale data center or telecom application

## Package Includes

N370-100M-AR 100Gb Duplex Singlemode 9/125 OS2 Armored Fiber Optic Cable, Yellow, 100 m (328 ft.)



Optical Mode	OS2
Mode Type	Singlemode
<b>PHYSICAL</b>	
Color	Blue; White; Yellow
Material of Construction	Outer Jacket: PVC (LSZH Rating); Inner Flexible Steel Tube: SUS204 (Armored)
Cable Jacket Color	Yellow
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Cable Outer Diameter (OD)	3.0MM
Clad Diameter (microns)	125
Core Diameter (microns)	9
Primary Coating Diameter (microns)	550
Number of Fibers	2
Cable Length (ft.)	328.1
Cable Length (m)	100.03
Cable Length (in.)	3937
Minimum Bend Radius	30mm
Shipping Dimensions (hwd / in.)	12.00 x 10.50 x 0.50
Shipping Weight (kg)	1.42
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 °F (-20 to 60 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Network Compatibility	10 Gbps; 25 Gbps; 40 Gbps; 100 Gbps
Wavelength	1310nm; 1550nm
Attenuation @ 1310NM	0.40dB/Km
Attenuation @ 1550NM	0.30dB/Km
Insertion Loss	0.30dB
<b>CONNECTIONS</b>	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)



Endface Polish	UPC
Connector Color	Blue; White
<b>FEATURES &amp; SPECIFICATIONS</b>	
Push/Pull Tabs	No
Optical Port	LC
Breakout	No
Trunk	No
Armored Cable	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS, REACH
Approvals	RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>