

## 400G Duplex Singlemode 9/125 OS2 Switchable Fiber Optic Cable (LC/UPC M/M), LSZH, Yellow, 6 m (19.7 ft.)

MODEL NUMBER: N370X-06M



400 GbE Ethernet cable with switchable LC connectors supports high bandwidths necessary for enterprise applications in wiring closets, telecom rooms and data centers.

### Features

#### 40/100/400 GbE Cable Supports Higher Bandwidths for High-Density Data Networking

The N370X-06M is a premium multimode fiber optic cable that supports 400 Gb Ethernet speeds for transmitting data and voice signals over short distances. It is designed to support higher bandwidths for high-density patching between data center MDFs and IDF in enterprise installations. This singlemode 9/125 OS2 cable is an ideal choice for 100 Gb Ethernet applications up to 100 meters (328 feet) at 1550 nm. It is also backward compatible with 10 Gb and 25 Gb networks, so you can future-proof your current application for an eventual upgrade to 100 Gb or 400 Gb.

#### Switchable Connectors Allow Easy Polarity Conversions

The switchable LC/UPC duplex ends let you easily switch the fiber polarity without tools or the need to re-terminate the connectors.

#### Yellow Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The OS2-rated cable has a yellow jacket to identify it as singlemode in a crowded patch panel or switch and prevent it from becoming accidentally disconnected. The round low-smoke zero-halogen (LSZH) jacket limits the amount of toxic smoke emitted in case of combustion, making it suitable for poorly ventilated areas.

## Specifications

| OVERVIEW     |              |
|--------------|--------------|
| UPC Code     | 037332271822 |
| Technology   | Singlemode   |
| Optical Mode | OS2          |

### Highlights

- OS2-rated cable recommended for 100 Gb speeds up to 100 meters (@ 1550 nm)
- Switchable LC connectors allow polarity conversion without tools or re-termination
- Backward compatible with 10/25/40 Gb networks to facilitate future-proofing
- Yellow LSZH jacket allows fast, easy identification in a crowded switch or patch panel

### Package Includes

N370X-06M 400G Duplex Singlemode 9/125 OS2 Switchable Fiber Optic Cable, Yellow, 6 m (19.7 ft.)

|                                      |  |
|--------------------------------------|--|
| Mode Type                            | Singlemode                                   |
| <b>PHYSICAL</b>                      |  |
| Cable Jacket Color                   | Yellow                                       |
| Connector Color                      | Blue   |
| Cable Jacket Material                | LSZH   |
| Cable Jacket Rating                  | OFNR   |
| Cable Outer Diameter (OD)            | 2.0 +/- 0.1 mm x 4.1 +/- 0.2 mm              |
| Clad Diameter (microns)              | 125.0  |
| Core Diameter (microns)              | 9.0  |
| Primary Coating Diameter (microns)   | 600.0  |
| Number of Fibers                     | 2  |
| Cable Length (ft.)                   | 19.68  |
| Cable Length (m)                     | 6.00   |
| Cable Length (in.)                   | 236.22                                       |
| Minimum Bend Radius                  | 20 mm (Dynamic); 10 mm (Static)              |
| Fiber Cable Length                   | 6M (19.7 ft)                                 |
| <b>ENVIRONMENTAL</b>                 |  |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C)                  |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C)                  |
| Relative Humidity                    | 5% to 85% RH, Non-Condensing                 |
| <b>COMMUNICATIONS</b>                |  |
| Network Compatibility                | 1 Gbps (Gigabit); 10 Gbps; 40 Gbps; 100 Gbps |
| Attenuation @ 1310NM                 | 0.4 dB/km                                    |
| Attenuation @ 1550NM                 | 0.3 dB/km                                    |
| Insertion Loss                       | 0.30 dB                                      |
| <b>CONNECTIONS</b>                   |  |
| Side A - Connector 1                 | LC DUPLEX (MALE)                             |
| Side B - Connector 1                 | LC DUPLEX (MALE)                             |
| Endface Polish                       | UPC  |
| Switchable Polarity                  | Yes  |
| <b>FEATURES &amp; SPECIFICATIONS</b> |  |
| Optical Port                         | LC   |

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

| STANDARDS & COMPLIANCE              |                           |
|-------------------------------------|---------------------------|
| Product Certifications              | UL 1666                   |
| Product Compliance                  | RoHS; CE (Europe); REACH  |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.