

Fiber TAP Cassette - Multimode, 4x Duplex LC, 70/30 Split

MODEL NUMBER: N482TAP-4MM73LC



Installs in Tripp Lite N482-Series chassis to split optical fiber signals into two outputs, one for user and one for monitoring.

Features

Fiber Optic TAP Cassette Helps You Monitor and Analyze Network Data

This Tripp Lite N482TAP-4MM73LC multimode TAP (traffic access point) cassette is a passive device added to a fiber optic network to enable real-time monitoring. Its optical splitter divides the optical signal into two outputs, one for the downstream device and one for monitoring, without introducing latency or creating a single point of failure.

Creates a 70/30 Split Ratio for User Traffic and Signal Monitoring

Network monitoring is used to gather data to analyze performance issues, optimize network traffic and uncover security threats in your data center, telecom carrier network or R&D facility. This TAP cassette directs 30 percent of the light to a nearby monitoring device. The remaining 70 percent is transmitted as usual throughout the network without affecting performance.

Compatible with Tripp Lite Multimode Cabling

This passive TAP cassette supports 40/100 Gb internally using multimode fiber optic cable, enabling you to perform monitoring and data analysis without causing delays or affecting network performance. It is compatible with recommended Tripp Lite cables, including the N820-Series, for connecting to switches, routers and monitoring equipment.

Easy to Install with Compatible Enclosures

The multimode N482TAP-4MM73LC works with Tripp Lite's N482-00U (fits one cassette), N482-01U (fits five cassettes), N482-02U (14 cassettes) and N482-04U (28 cassettes) chassis. The futureproof-friendly modular design allows you to remove the cassette without replacing the panel or removing other cassettes. The TAP cassette also complies with IEEE 802.3ae (10 Gb) and ANSI T11.2 (Fibre Channel) requirements. A 0.20 dB maximum insertion loss falls under IEEE 802.3ae maximum channel loss spec of <25 dB.

Factory-Terminated Ports Help Reduce Installation Time

The OM4-rated cassette has 12 Duplex LC ports that allow fast, easy connection of cables. The durable plastic cassette comes with dust caps to protect unused ports.

Specifications

Highlights

- Passive OM4 multimode fiber TAP with 40/100 Gb LC to LC ports
- 70/30 split ratio allows real-time traffic analysis while preserving primary link performance
- Fiber TAP cassette is optimized for parallel optics and Base-8 connectivity
- Compatible with Tripp Lite N482-00U, N482-01U, N482-02U and N482-04U panels

Applications

Monitor network activity for performance or security issues while allowing the normal flow of traffic

System Requirements

- Compatible with recommended Tripp Lite cables, including N820-Series
- Works with Tripp Lite N482-Series fiber enclosure panels

Package Includes

- N482TAP-4MM73LC Multimode TAP Cassette, 70/30
- Quick Start Guide



OVERVIEW	
UPC Code	037332262608
Product Type	Passive Fiber TAP
Technology	Multimode
Optical Mode	OM4
PHYSICAL	
Number of Fibers	8
Shipping Dimensions (hwd / in.)	2.00 x 7.90 x 4.70
Shipping Weight (lbs.)	0.44
Unit Dimensions (hwd / in.)	4.72 x 3.46 x 1.18
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 °F (-20 to 60 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
Relative Humidity	5 to 85% RH, Non-Condensing
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit); 400 Gbps
Wavelength	850nm
Insertion Loss	3.00 dB / 7.00 dB @ 850nm (INCLUDE CONNECTOR)
Split Ratio	70/30
CONNECTIONS	
Monitoring Ports	4
Side A - Connector 1	LC DUPLEX (FEMALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
Input Ports	4
Output Ports	4
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>