

## Fiber TAP Cassette - Singlemode, 4x Duplex LC, 70/30 Split

MODEL NUMBER: N482TAP-4SM73LC



Helps you gather data to analyze performance issues, optimize network traffic and monitor a fiber network for security threats.

### Features

#### Fiber Optic TAP Cassette Helps You Monitor and Analyze Network Data

This N482TAP-4SM73LC singlemode TAP (traffic access point) cassette is a passive device added to a fiber optic network to enable real-time monitoring. Its optical splitter divides the optical signal into two outputs, one for the downstream device and one for monitoring, without introducing latency or creating a single point of failure.

#### Creates a 70/30 Split Ratio for User Traffic and Signal Monitoring

Network monitoring is used to gather data to analyze performance issues, optimize network traffic and uncover security threats in your data center, telecom carrier network or R&D facility. This TAP cassette directs 30 percent of the light to a nearby monitoring device. The remaining 70 percent is transmitted as usual throughout the network without affecting performance.

#### Compatible with Singlemode Cabling

This passive TAP cassette supports 40/100 Gb internally using singlemode fiber optic cable, enabling you to perform monitoring and data analysis without causing delays or affecting network performance. It is compatible with recommended cables, including the N370-Series, for connecting to switches, routers and monitoring equipment.

#### Easy to Install with Compatible Enclosures

The singlemode N482TAP-4SM73LC works with N482-00U (fits one cassette), N482-01U (fits five cassettes), N482-02U (14 cassettes) and N482-04U (28 cassettes) chassis. The futureproof-friendly modular design allows you to remove the cassette without replacing the panel or removing other cassettes. The TAP cassette also complies with IEEE 802.3ae (10 Gb) and ANSI T11.2 (Fibre Channel) requirements. A 0.20 dB maximum insertion loss falls under IEEE 802.3ae maximum channel loss spec of <25 dB.

#### Factory-Terminated Ports Help Reduce Installation Time

The OM4-rated cassette has 12 Duplex LC ports that allow fast, easy connection of cables. The durable plastic cassette comes with dust caps to protect unused ports.

## Specifications

### Highlights

- Passive OM4 singlemode fiber TAP with 40/100 Gb LC to LC ports
- 70/30 split ratio allows real-time traffic analysis while preserving primary link performance
- Fiber TAP cassette is optimized for parallel optics and Base-8 connectivity
- Compatible with N482-00U, N482-01U, N482-02U and N482-04U panels

### Applications

Monitor network activity for performance or security issues while allowing the normal flow of traffic

### System Requirements

- Compatible with recommended cables, including N370-Series
- Works with N482-Series fiber enclosure panels

### Package Includes

- N482TAP-4SM73LC Singlemode TAP Cassette, 70/30
- Quick Start Guide

| <b>OVERVIEW</b>                     |  |
|-------------------------------------|--|
| UPC Code                            | 037332262592                                   |
| Product Type                        | Passive Fiber TAP                              |
| Technology                          | Singlemode                                     |
| Optical Mode                        | OM4  |
| <b>PHYSICAL</b>                     |  |
| Number of Fibers                    | 8  |
| Shipping Dimensions (hwd / in.)     | 2.00 x 7.90 x 4.70                             |
| Shipping Weight (lbs.)              | 0.44   |
| Unit Dimensions (hwd / in.)         | 4.720 x 3.460 x 1.180                          |
| <b>ENVIRONMENTAL</b>                |  |
| Operating Temperature Range         | -4° to 140°F (-20° to 60°C)                    |
| Storage Temperature Range           | -4° to 140°F (-20° to 60°C)                    |
| Relative Humidity                   | 5% to 85% RH, Non-Condensing                   |
| <b>COMMUNICATIONS</b>               |  |
| Network Compatibility               | 1 Gbps (Gigabit); 400 Gbps                     |
| Wavelength                          | 1550nm   |
| Insertion Loss                      | 2.60 dB / 6.60 dB @ 1550nm (INCLUDE CONNECTOR) |
| Split Ratio                         | 70/30  |
| <b>CONNECTIONS</b>                  |  |
| Monitoring Ports                    | 4  |
| Side A - Connector 1                | LC DUPLEX (FEMALE)                             |
| Side B - Connector 1                | LC DUPLEX (FEMALE)                             |
| Input Ports                         | 4  |
| Output Ports                        | 4  |
| <b>STANDARDS &amp; COMPLIANCE</b>   |  |
| Product Compliance                  | RoHS; REACH                                    |
| <b>WARRANTY &amp; SUPPORT</b>       |  |
| Product Warranty Period (Worldwide) | Lifetime limited warranty                      |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.