

# Preloaded Fiber Patch Panel, 3U - 64x (12F MTP/MPO-PC to 4x LC Duplex F/F) 8F Trunk Cables, OM4 Multimode, 3 m (9.8 ft.)

MODEL NUMBER: N48M-64M8L4-03



3U patch panel comes preloaded with spools of multimode fiber cable that allow you to extend the exact length required and store the excess out of sight.

## Description

Preloaded Fiber Patch Panel, 3U - 64x (12F MTP/MPO-PC to 4x LC Duplex F/F) 8F Trunk Cables, OM4 Multimode, 3 m (9.8 ft.)

## Features

### 3U Panel Solution Comes with Cabling Preloaded to Cut Costs and Save Time

All necessary cabling is included with this preloaded fiber panel, coiled inside and ready for immediate use. The aluminum 3U chassis features 64 MTP/MPO-PC to LC Duplex 8-fiber multimode trunk cables, all three meters (9.8 feet) in length to make management easy. The panel opens to provide easy access to stored cables. Use only as much cabling as you need. The remainder stores inside the chassis to eliminate cable clutter, allow better airflow through the rack and make equipment maintenance and replacement easier. The cables and panels have labels to help with organization. You also avoid the expense and effort of custom cabling. The flexibility in cable length lets you reuse the cables if equipment is moved.

### Integrates Equipment to Meet Current Connectivity Needs

This preloaded slack-free panel helps integrate your 10 Gb equipment with 40 Gb networks or 25 Gb equipment with 100 Gb networks in a simple, elegant and flexible manner. The N48M-64M8L4-03 mounts in just 3U of space in an EIA-standard 19-inch rack.

## Specifications

OVERVIEW	
UPC Code	037332262233
Product Type	Preloaded
Technology	Multimode
Optical Mode	OM4

## Highlights

- 64 MTP/MPO-to-LC 8-fiber OM4 multimode cables come coiled inside for instant use
- Use only as much cable as you need; store the remainder inside to avoid clutter
- Flexible cable length allows reuse of cables if equipment is moved
- 256 LC Duplex ports protected by fold-down front panel with organization labels
- Aluminum chassis mounts into 3U of space in EIA-standard 19 in. racks

## Applications

- Integrate 10G equipment with a 40G network or 25G equipment with a 100G network
- Save the expense and effort of buying custom cables or repurchasing cables after moving rack equipment
- Eliminate cable clutter by using only as much as you need and storing excess cable inside the panel

## Package Includes

- N48M-64M8L4-03 Preloaded Fiber Patch Panel
- (64) MTP/MPO-PC to LC Duplex trunk cables, 3 m (9.8 ft.)
- Installation guide



Powering Business Worldwide

TRIPP LITE  
SERIES

Panel Dimensions	17.42" X 5.24" X 12.99"
Panel Cable Number	64
Panel Cable Length (m)	3
Mode Type	Multimode
<b>Firmware / Software Docs</b>	
Offset Ports	No
<b>CONNECTIONS</b>	
Side A - Connector 1	(64) 12F MPO (FEMALE)
Side B - Connector 1	(256) LC DUPLEX (FEMALE)
Endface Polish	PC
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Rack Height	3U
Cable Jacket Color	Aqua
Cable Jacket Rating	OFNP
Cable Outer Diameter (OD)	2.9 mm
Clad Diameter (microns)	125
Core Diameter (microns)	50
Primary Coating Diameter (microns)	245
Number of Fibers	8
Cable Length (ft.)	9.8
Cable Length (m)	2.99
Cable Length (in.)	118.1
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Shipping Dimensions (hwd / in.)	8.90 x 22.80 x 18.90
Shipping Weight (lbs.)	18.96
Shipping Weight (kg)	8.60
Unit Dimensions (hwd / in.)	5.230 x 17.400 x 12.990
Fiber Cable Length	3M (9.8 ft)
Panel Style	Preloaded Fiber Panel
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)



Powering Business Worldwide

TRIPP LITE  
SERIES

Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Network Compatibility	40 Gbps; 100 Gbps; 400 Gbps
Wavelength	1300nm; 850nm
Attenuation @ 850NM	3.0 dB / km
Attenuation @ 1300NM	1.0 dB / km
Insertion Loss	MTP/MPO: 0.35 dB; LC: 0.20 dB
<b>FEATURES &amp; SPECIFICATIONS</b>	
All-in-One Kit	Yes
Push/Pull Tabs	Yes
Numbered Ports	Yes
Built-in Cables	Yes
Optical Port	LC; MPO/MTP
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.