

Preloaded Fiber Patch Panel, 3U - 64x (12F MTP/MPO-PC to 4x LC Duplex F/F) 8F Trunk Cables, OM4 Multimode, 3 m (9.8 ft.)

MODEL NUMBER: N48M-64M8L4-03



3U patch panel comes preloaded with spools of multimode fiber cable that allow you to extend the exact length required and store the excess out of sight.

Description

Preloaded Fiber Patch Panel, 3U - 64x (12F MTP/MPO-PC to 4x LC Duplex F/F) 8F Trunk Cables, OM4 Multimode, 3 m (9.8 ft.)

Features

3U Panel Solution Comes with Cabling Preloaded to Cut Costs and Save Time

All necessary cabling is included with this preloaded fiber panel, coiled inside and ready for immediate use. The aluminum 3U chassis features 64 MTP/MPO-PC to LC Duplex 8-fiber multimode trunk cables, all three meters (9.8 feet) in length to make management easy. The panel opens to provide easy access to stored cables. Use only as much cabling as you need. The remainder stores inside the chassis to eliminate cable clutter, allow better airflow through the rack and make equipment maintenance and replacement easier. The cables and panels have labels to help with organization. You also avoid the expense and effort of custom cabling. The flexibility in cable length lets you reuse the cables if equipment is moved.

Integrates Equipment to Meet Current Connectivity Needs

This preloaded slack-free panel helps integrate your 10 Gb equipment with 40 Gb networks or 25 Gb equipment with 100 Gb networks in a simple, elegant and flexible manner. The N48M-64M8L4-03 mounts in just 3U of space in an EIA-standard 19-inch rack.

Specifications

OVERVIEW	
UPC Code	037332262233
Product Type	Preloaded

Highlights

- 64 MTP/MPO-to-LC 8-fiber OM4 multimode cables come coiled inside for instant use
- Use only as much cable as you need; store the remainder inside to avoid clutter
- Flexible cable length allows reuse of cables if equipment is moved
- 256 LC Duplex ports protected by fold-down front panel with organization labels
- Aluminum chassis mounts into 3U of space in EIA-standard 19 in. racks

Applications

- Integrate 10G equipment with a 40G network or 25G equipment with a 100G network
- Save the expense and effort of buying custom cables or repurchasing cables after moving rack equipment
- Eliminate cable clutter by using only as much as you need and storing excess cable inside the panel

Package Includes

- N48M-64M8L4-03 Preloaded Fiber Patch Panel
- (64) MTP/MPO-PC to LC Duplex trunk cables, 3 m (9.8 ft.)
- Installation guide



Technology	Multimode
Optical Mode	OM4
Panel Dimensions	17.42" X 5.24" X 12.99"
Panel Cable Number	64
Panel Cable Length (m)	3
Fiber Panel Ports	(256) LC Duplex; (64) MTP/MPO
Mode Type	Multimode
Firmware / Software Docs	
Offset Ports	No
PHYSICAL	
Primary Form Factor	Rackmount
Cable Jacket Color	Aqua
Cable Jacket Rating	OFNP
Cable Outer Diameter (OD)	2.9MM
Clad Diameter (microns)	125
Core Diameter (microns)	50
Primary Coating Diameter (microns)	245
Number of Fibers	8
Cable Length (ft.)	9.8
Cable Length (m)	2.99
Cable Length (in.)	118.1
Minimum Bend Radius	20MM (DYNAMIC); 10MM (STATIC)
Rack Height	3U
Shipping Dimensions (hwd / in.)	8.90 x 22.80 x 18.90
Shipping Weight (kg)	8.60
Shipping Weight (lbs.)	18.96
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (-20 TO 60 C)
Storage Temperature Range	-4 TO 140 F (-20 TO 60 C)
Operating Humidity Range	5% TO 85% RH, NON-CONDENSING
Storage Humidity Range	5% TO 85% RH, NON-CONDENSING
COMMUNICATIONS	
Network Compatibility	10 Gbps; 40 Gbps; 100 Gbps; 400 Gbps



Wavelength	1300nm; 850nm
Attenuation @ 850NM	3.0dB/KM
Attenuation @ 1300NM	1.0dB/KM
Insertion Loss	MTP/MPO: 0.35dB; LC: 0.20dB
CONNECTIONS	
Side A - Connector 1	(64) MTP/MPO (FEMALE)
Side B - Connector 1	(256) LC DUPLEX (FEMALE)
Endface Polish	PC
FEATURES & SPECIFICATIONS	
Push/Pull Tabs	Yes
All-in-One Kit	Yes
Built-in Cables	Yes
Numbered Ports	Yes
Optical Port	LC; MPO/MTP
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>