


# Preloaded Fiber Panel, 1U - 2x (3x8F MTP/MPO-APC F/F) 24F Trunk Cables, OS2 Singlemode, 20 m (65.6 ft.)

MODEL NUMBER: N48S-2M3X8M-20



1U panel comes preloaded with spools of singlemode fiber cable that allow you to extend the exact length required and store the excess out of sight.

## Description

Preloaded Fiber Panel, 1U - 2x (3x8F MTP/MPO-APC F/F) 24F Trunk Cables, OS2 Singlemode, 20 m (65.6 ft.)

## Features

### 1U Panel Solution Comes with Cabling Preloaded to Cut Costs and Save Time

All necessary cabling is included with this preloaded fiber panel, coiled inside and ready for immediate use. The aluminum 1U chassis features two 24-fiber MTP/MPO-APC singlemode trunk cables, both 20 meters (65.6 feet) in length to make management easy. The panel opens to provide easy access to stored cables. Use only as much cabling as you need. The remainder stores inside the chassis to eliminate cable clutter, allow better airflow through the rack and make equipment maintenance and replacement easier. The cables and panels have labels to help with organization. You also avoid the expense and effort of custom cabling. The flexibility in cable length lets you reuse the cables if equipment is moved. The N48S-2M3X8M-20 mounts in just 1U of space in an EIA-standard 19-inch rack.

## Highlights

- Dual MTP/MPO-APC 24-fiber OS2 singlemode cables come coiled inside for instant use
- Use only as much cable as you need; store the remainder inside to avoid clutter
- Flexible cable length allows reuse of cables if equipment is moved
- Aluminum chassis mounts into 1U of space in EIA-standard 19 in. racks

## Applications

- Save the expense and effort of buying custom cables or repurchasing cables after moving rack equipment
- Eliminate cable clutter by using only as much as you need and storing excess cable inside the panel

## Package Includes

- N48S-2M3X8M-20 Preloaded Fiber Panel
- (2) MTP/MPO-APC to MTP/MPO-APC trunk cables, 20 m (65.6 ft.)
- Installation guide

## Specifications

OVERVIEW	
UPC Code	037332262714
Product Type	Preloaded
Technology	Singlemode
Optical Mode	OS2
Panel Dimensions	17.32" X 1.73" X 10.20"
Panel Cable Number	2
Panel Cable Length (m)	20



Powering Business Worldwide

TRIPP LITE  
SERIES

Mode Type	Singlemode
<b>Firmware / Software Docs</b>	
Offset Ports	No
<b>CONNECTIONS</b>	
Side A - Connector 1	(3) 12F MPO (FEMALE)
Side B - Connector 1	(3) 12F MPO (FEMALE)
Endface Polish	APC
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Rack Height	1U
Cable Jacket Color	Yellow
Connector Color	Black; Green
Cable Jacket Material	PVC
Cable Jacket Rating	OFNP
Cable Outer Diameter (OD)	2.9 mm
Clad Diameter (microns)	125
Core Diameter (microns)	9
Primary Coating Diameter (microns)	245
Number of Fibers	24
Cable Length (ft.)	65.6
Cable Length (m)	20.00
Cable Length (in.)	787.4
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Shipping Dimensions (hwd / in.)	4.30 x 22.80 x 18.90
Shipping Weight (kg)	3.50
Fiber Cable Length	20M (65.6 ft)
Panel Style	Preloaded Fiber Panel
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Network Compatibility	40 Gbps; 100 Gbps; 400 Gbps
Wavelength	1310nm; 1550nm
Attenuation @ 1310NM	0.36 dB / km
Attenuation @ 1550NM	0.22 dB / km
Insertion Loss	0.30 dB
<b>FEATURES &amp; SPECIFICATIONS</b>	
All-in-One Kit	Yes
Push/Pull Tabs	Yes
Built-in Cables	Yes
Optical Port	MPO/MTP
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.