

36-Port Fiber Patch Panel Enclosure, 1U Rack-Mount (LC/LC)

MODEL NUMBER: N492-036-LCLC-E



Highlights

- Supports up to 36 LC/LC patch connections
- Multimode and most Singlemode applications supported
- Space saving 1U design, 19" rackmountable

Package Includes

- 1U Chassis
- 3 x 12-port LC Feed-Through Adapter plate
- Mounting Brackets
- Mounting Screws

Description

Tripp Lite N492-036-LCLC-E is a pre-loaded, 36-port, LC/LC fiber patch enclosure that supports either Multimode or most Singlemode LC Fiber cable patching. Features rugged heavy steel construction, with multiple rear entry points for trunk cable feeding into the panel, providing protection as well as internal management. 1U design takes up minimal space while allowing for maximum patching.

Features

- 36 port LC/LC Feed Through couplers in a 1U panel (3 x 12port modules)
- Supports most Singlemode and Multimode Fiber connections
- 19" Wide x 8" Deep x 1.75" High
- Pull-out locking tray for easy access to internal connections
- Heavy Cold-Rolled steel construction, Black Powder Coated finish
- Six rear cable entry ports
- Adjustable depth mounting

Specifications

OVERVIEW	
UPC Code	037332181824
Product Type	Feed-Through
Technology	Singlemode; Multimode
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	20.90 x 1.80 x 9.80

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Shipping Dimensions (hwd / cm)	53.09 x 4.57 x 24.89
Shipping Weight (lbs.)	6.00
Shipping Weight (kg)	2.72
Unit Dimensions (hwd / in.)	1.700 x 19.000 x 1.250
Unit Dimensions (hwd / cm)	4.445 x 48.26 x 20.32
CONNECTIONS	
Number of Ports	36
Side A - Connector 1	LC DUPLEX (FEMALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.