

## Duplex Multimode 50/125 Fiber Patch Cable (LC/ST), 15M (50 ft.)

MODEL NUMBER: **N518-15M**



### Description

Tripp Lite's 15-meter ( 50ft ) multimode duplex fiber optic LC/ST patch cable is manufactured from 50/125 zipcord fiber. The cable has LC connectors on one end, and ST connectors on the other. It has a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in fiber and Fibre Channel applications. It is backward compatible with 62.5 micron fiber and built-in headroom for future applications. The cable provides higher bandwidth optimized for Gigabit and 10Gbps networks.

### Features

- Constructed with 50/125 micron cable
- Length - 15M ( 50ft )
- Use on fiber and fibre channel installations
- LC male to ST male connectors
- Higher bandwidth optimized for gigabit and 10Gbps networks
- Backward compatible with 62.5 micron fiber
- Built-in headroom for future applications

## Specifications

OVERVIEW	
UPC Code	037332134769
Clad Diameter	125 micron
Core Diameter	50 micron
Number of Fibers	2
Technology	Multimode

### Highlights

- Premium PVC multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Perfect for use with Fibre Channel Controller Cards and Switches

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/ST connectors

### Package Includes

- 15M ( 50ft ) duplex MMF cable LC/ST 50/125 fiber



Optical Mode	OM2
<b>INPUT</b>	
Cable Length (ft.)	49.2
Cable Length (m)	15
Cable Length (in.)	590.6
<b>PHYSICAL</b>	
Color	Orange
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 2.54
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 1.00
Shipping Weight (kg)	0.08
Shipping Weight (lbs.)	0.18
<b>COMMUNICATIONS</b>	
Network Speed	1Gbps
<b>CONNECTIONS</b>	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	ST DUPLEX (MALE)
<b>SPECIAL FEATURES</b>	
Push/Pull Tabs	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	FDDI and OFNR rated
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>