

## 5-Port Unmanaged Industrial Gigabit Ethernet Switch - 10/100/1000 Mbps, DIN/Wall Mount

MODEL NUMBER: NGI-U05



Industrial-grade switch expands Ethernet connectivity to factory floors and other environments with space constraints and wide temperature ranges.

### Features

#### 5-Port Unmanaged Gigabit Ethernet Switch Connects Your Devices to a LAN

This space-saving Tripp Lite switch transmits data over a Gigabit Ethernet network. Five auto-negotiating 10/100/1000 Mbps ports send data only to the devices designated to receive it, which improves the efficiency and potential throughput of the network.

#### Ruggedized Metal Housing Built to Last in Harsh Environments

The compact NGI-U05 adds 10/100/1000 Mbps Gigabit Ethernet capacity to your industrial and commercial applications, such as factory floors, warehouse operations and other environments with space constraints and wide temperature ranges. The industrial-grade high-strength case withstands vibration, shock and free fall. It can also operate in extreme temperatures ranging from -40 degrees to 167 degrees Fahrenheit.

#### Unmanaged Switch Requires Little to No Configuration

Quickly connect your network devices with little to no configuration. LEDs indicate when the switch is powered on and which Ethernet ports are showing activity. The NGI-U05 supports MAC address auto-learning and auto-aging for efficient routing, as well as automatic MDI/MDI-X crossover detection for plug-and-play functionality. IEEE 802.3x flow control allows smooth transmission of large files.

#### Works with the Most Popular Web Browsers

The NGI-U05 is browser-based and works independently from the connected computer's operating system. Because switch compatibility is based on common hardware standards, rather than system software dependencies, the NGI-U05 accommodates most platforms. Preferred web browsers include Google Chrome (on both Windows and macOS) and Microsoft Edge (Windows only).

#### Flexible Mounting Options

The NGI-U05 may be DIN mounted using the pre-installed rail clip, which mounts firmly to any standard 35 mm DIN rail. It may also be wall mounted vertically or horizontally using the rear mounting holes. A 3-pin 9-48VDC terminal block supplies power input. Device power must be supplied by LPS (Limited Power Source) circuit.

#### TAA-Compliant for GSA Schedule Purchases

The NGI-U05 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA

### Highlights

- 5 auto-negotiable 10/100/1000 Mbps RJ45 ports connect devices over a LAN
- Industrial-grade switch supports operating temperature range of -40° to 167°F
- Easy-to-read LEDs indicate connection and activity status for all Ethernet ports
- Plug-and-play operation with no software or configuration required before use
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

Expand reliable Gigabit Ethernet connectivity to factory floors and outdoor environments with space constraints and wide temperature ranges

### Package Includes

- NGI-U05 5-Port Unmanaged Industrial Gigabit Switch
- DIN rail-mounting clip (pre-installed)
- Wall-mounting bracket (pre-installed)
- Owner's manual

(General Services Administration) Schedule and other federal procurement contracts.

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332265838
Product Type	Unmanaged Industrial Gigabit Ethernet Switch
<b>INPUT</b>	
Maximum Input Amps Details	Maximum of 0.5A DC. The device power shall be supplied by SLPS (Limited Power Source)
Voltage Compatibility (VDC)	From 9-48
Power Source	3-Pin Terminal Block
<b>POWER</b>	
Power Consumption (Watts)	4.00
Power Consumption Detail	4
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	1- Power ON/OFF (GREEN), 2- 100Mbps(GREEN) for Ethernet speed 10/100Mbps & Data Transmitting/Receiving, 3- 1000 (GREEN) for Ethernet speed 1000Mbps & Data Transmitting/Receiving
<b>PHYSICAL</b>	
Primary Form Factor	Din-Rail; Wall-mount
Color	Black
Material of Construction	Aluminum casing
Form Factors Supported	Din-Rail & Wall Mountable
Included Mounting Accessories	Y
Shipping Dimensions (hwd / in.)	2.44 x 5.04 x 9.33
Shipping Dimensions (hwd / cm)	6.20 x 12.80 x 23.70
Shipping Weight (lbs.)	0.71
Shipping Weight (kg)	0.32
Unit Dimensions (hwd / in.)	4.300 x 0.920 x 2.910
Unit Dimensions (hwd / cm)	10.9 x 2.2 x 7.3
Unit Weight (lbs.)	0.44
Unit Weight (kg)	0.20
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-40°F TO 167°F (-40°C TO 75°C)

Storage Temperature Range	-40°F to 185°F (-40°C to 85°C)
Relative Humidity	5% to 95% (Non-Condensing)
Operating Elevation (m)	2000
ESD Protection	±8kV air discharge / ±4kV contact discharge
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit)
Network Compatibility Details	Auto-negotiable
Switching Capacity	10Gbps
Switching Capacity Details	1Gbps Per Port with Full Duplex
<b>CONNECTIONS</b>	
Number of Ports	5
RJ45 Ports	5
RJ45 Ports Detail	5x 10/100/1000BASE-T
Network Switch Ports	(5) 10/100/1000 (RJ45)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Fans (Type/Quantity)	Fanless
MAC Addresses	2000
Jumbo Frames	9000
Console Port	No
MAC Auto Learning	Yes
RMON	No
SNMP	No
Storm Control	No
DHCP Snooping	No
Auto MDI/MDIX Crossover Detection	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); IEEE 802.3 10Base-T; IEEE 802.3 Auto-Negotiation; IEEE 802.3u 100Base-TX/FX; IEEE 802.3x Flow Control; REACH; FCC (USA); Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2022 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.