


## 24 10/100/1000Mbps Port Gigabit L2 Web-Smart Managed PoE+ Switch, 240W; 2 Dedicated SFP Gigabit Slots, 52 Gbps, 12-Outlet 120V PDU

MODEL NUMBER: **NSS-G24D2P24**



Combines a managed 24-port PoE+ Gigabit network switch with a basic PDU/surge protector in one 1U rack-mount unit. Ideal for monitoring and controlling an LAN and powering equipment in a small-to-medium distributed network.

### Description

The energy-efficient NSS-G24D2P24 24-Port PoE+ Gigabit L2 Web-Smart Managed Network Switch does more than complete your home or office LAN. It also features a basic 120V 15A PDU to distribute reliable AC power to critical IT equipment in your wiring closet, server room or equipment rack. Two dedicated SFP ports are also included for uplinking data to other switches via optical fiber or copper.

This switch features 24 twisted-pair RJ45 Gigabit Ethernet ports that support auto-negotiable 10/100/1000 Mbps and auto MDI/MDIX cross-over detection functions for convenient plug-and-play capability. Each port can be configured to supply up to 30W of PoE+ (Power over Ethernet) power via network cable to connected devices, such as VoIP phones and video cameras. Easy-to-read LEDs indicate connection and activity status for each port. Built-in management software lets you monitor and control each connected device via secure web-based interface. Each port supports up to 2 Gbps with full duplex.

The rear panel contains 12 NEMA 5-15R outlets that supply continuous power to connected devices. Your equipment is protected by 3860 joules of Isobar surge suppression, as well as front-panel LEDs that let you monitor line status at a glance. A 12A circuit breaker trips if the current drawn by connected equipment exceeds the PDU's maximum load rating.

The NSS-G24D2P24 supports IEEE802.3az Energy Efficient Ethernet standards. The heavy-duty metal housing mounts into 1U of an EIA-standard 19-inch rack using the included hardware.

### Features

**Enterprise Managed Network Switch** 24 twisted-pair RJ45 Gigabit Ethernet ports  
Auto-negotiable 10/100/1000 Mbps  
Automatic MDI/MDIX cross-over detection  
52 Gbps switching capacity (2 Gbps per port with full duplex)  
Easy-to-read LEDs indicate connection, activity and PoE status for each port  
Supports 10k jumbo frames  
Supports MAC address auto-learning and auto-aging up to 16,000 addresses  
Advanced Enterprise level, L2 management features

**240W Total PoE+ Budget** Each port can be configured to supply PoE+ power via network cable to connected devices, such as VoIP phones and video cameras  
30W max per port

**Advanced Network Monitoring** Built-in Ethernet network interface allows full remote access for monitoring, configuration and control and notifications via web browser  
VLAN, trunking and other features improve switch's and network's efficiency and performance

**Basic 120V 15A PDU** 12 NEMA 5-15R rear outlets supply continuous power to connected devices  
3860 joules of Isobar surge suppression  
Front-panel LEDs indicate protection, fault, and line status  
40-80 dB

### Highlights

- 24 PoE+ ports with 2 dedicated SFP slots, 52 Gbps switching capacity, 240W PoE+ budget
- Enterprise-level security and layer 2 management
- IP-MAC-Port-Binding, ACL, Storm Control, Port Security, DHCP Snooping, 802.1x, L2
- WEB management, SNMP, RMON features
- Built-in 12-outlet PDU with 3860-joule surge protection rating

### Package Includes

- NSS-G24D2P24 24-Port Gigabit L2 Web-Smart Managed Network Switch
- Rack-mounting hardware
- Owner's manual



EMI/RFI noise reduction

**Dual Dedicated SFP Ports** Connect two SFP (Mini-GBIC) transceiver modules for uplinking to other switches via optical fiber or copper LEDs indicate interface traffic

**Compliant with Energy Efficient Ethernet standards** Automatically shifts unused ports to low power state without interrupting network connection Meets IEEE 802.3ab, 802.3i, 802.3u, 802.3x, 802.3, 802.1q, 802.1d, 802.1w, 802.3ad and 802.3az standards

**Mounts Horizontally in 1U of Rack Space** Compatible with EIA-standard 19 in. racks and rack enclosures NEMA 5-15P plug with 6 ft. AC power cord

## Specifications

OVERVIEW	
UPC Code	037332195302
PDU Type	Basic
INPUT	
Electrical Consumption	PDU supports up to 12A total; Network switch consumes up to 305 watts (with a maximum POE load of 240 watts)
PDU Input Voltage	100; 120; 127
PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output Circuit Breakers	12A
Output Receptacles	(12) 5-15R
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 included switches enable HARD factory reset and SOFT factory reset options
LED Indicators	Power LED (Green for Power On); Three LEDs per RJ-45 port (Green indicates 10/100Mbps link; Amber indicates 1000Mbps link; Green indicates POE status; LEDs flash to indicate port activity); Two LEDs indicate SFP connection (Green); One LED indicates system status (Green); Set of 3 LEDs indicate surge suppression status (Green: Protection Present / Red: Fault / Green: Line OK)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3860
Protection Modes	L-N, L-G, N-G
Clamping Voltage (RMS)	330
EMI / RFI Filtering	40-80dB
PHYSICAL	
Color	Black



**Tripp Lite**  
 1111 W. 35th Street  
 Chicago, IL 60609 USA  
 Telephone: 773.869.1234  
 www.tripplite.com

Minimum Required Rack Depth (cm)	39.12
Minimum Required Rack Depth (inches)	15.4
PDU Form Factor	Horizontal (1U)
Primary Form Factor	Rackmount
Shipping Dimensions (hwd / cm)	11.68 x 42.93 x 52.58
Shipping Dimensions (hwd / in.)	4.60 x 16.90 x 20.70
Shipping Weight (kg)	6.17
Shipping Weight (lbs.)	13.60
Unit Dimensions (hwd / cm)	4.34 x 44 x 31.5
Unit Dimensions (hwd / in.)	1.71 x 17.32 x 12.4
Unit Weight (kg)	4.90
Unit Weight (lbs.)	10.80
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	5 to 95% (Non-condensing)
Operating Elevation (ft.)	10,000
Operating Temperature	32 to 104 F (0 to 40 C)
Operating Elevation (m)	3,000
<b>CONNECTIONS</b>	
Ports	26
Network Switch Ports	(24) 10/100/1000 (RJ45); (2) Dedicated SFP; (1) Console (RJ45)
PoE Supported Ports	24
PoE Capability	15.4W (802.3af); 30W (802.3at)
PoE Power Budget (Watts)	240
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Compliant standards: IEEE 802.3ab (1000BASE-T GIGABIT ETHERNET), IEEE 802.3i (10BASE-T ETHERNET), IEEE 802.3u (100BASE-T ETHERNET), IEEE 802.3x (FULL DUPLEX/FLOW CONTROL), IEEE 802.3 (NWAY AUTO-NEGOTIATION), 802.1Q (TAGGED VLAN), 802.1D (STP), 802.1w (RSTP), 802.3ad (LACP), 802.3az (ENERGY EFFICIENT ETHERNET), 802.3at (POWER OVER ETHERNET)
Approvals	Tested to: UL 60950-1, UL 1449 3rd Edition, CAN/CSA-C22.2 No. 60950-1, FCC Part 15 Class A, NOM
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>