

## OmniSmart LCD 120V 900VA 475W Line-Interactive UPS, Tower, LCD display, USB port

MODEL NUMBER: OMNI900LCD



### Description

Tripp Lite's OMNI900LCD Line-Interactive Digital UPS System offers voltage regulation, surge suppression and long lasting battery support for personal computers, home entertainment systems and media centers. Internal UPS circuits support entry level PCs for up to 50 minutes or individual VCR/DVR components for as long as 2.5 hours during power failures. Prevents data loss, viewing interruptions, lost recordings and loss of component programming. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. 97% line-mode efficiency saves energy and reduces BTU heat output. Offers complete power protection in an attractive black tower configuration. Includes 4 battery-supported and surge-protected outlets, plus 4 additional surge suppression-only outlets for items not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert software available via free download. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Built-in audible alarm and large LCD front panel voltage display indicates line power status, battery power status, battery low/replace status and voltage boost operation. The LCD display includes a dimmer switch and can be rotated for easy viewing in any application. 900VA/475 watt power handling ability supports entry-level PCs, home entertainment systems, network workstations, audio/video components. Offers 3 minutes battery runtime with a full load of 900VA/475 watts and 10 minutes with a half load of 450VA/237 watts. Supports battery replacement via built-in access panel. \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- LCD Display with dimmer switch indicates input voltage, battery capacity and a variety of operating conditions. Display is rotatable for easy viewing whether UPS is in vertical or horizontal position
- OMNI900LCD Digital Uninterruptible Power Supply offers voltage regulation, surge suppression and long lasting battery support during blackouts
- Supports entry level PCs up to 50 minutes or single VCR/DVR components for up to 2.5 hours during

### Highlights

- 900VA tower 120V line interactive UPS with LCD display
- Corrects brownouts as low as 89V without using battery power
- LCD screen reports input voltage, battery charge and UPS status
- USB port, Surge-only outlets, 97% efficiency
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets

### Package Includes

- OMNI900LCD UPS System
- Instruction manual



blackouts

- 97% line-mode efficiency saves energy and reduces BTU heat output
- Regulates brownouts as low as 89 volts back to usable levels without using battery power
- 4 UPS battery-supported and surge-protected outlets, plus 4 additional surge suppression-only outlets
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert) (user supplies cable)
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- 900VA/475 watt power handling ability supports a variety of sensitive computer, home theater and other equipment
- 3 minutes full load runtime (900VA/475 watts), 10 minutes half load runtime (450VA/237 watts)
- Cabinet adapts to tower format or rackmount shelf format. Rackmount (2U) format requires an optional shelf, available separately
- Supports battery replacement via built-in access panel
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332125156
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	900
Output Watt Capacity (Watts)	475
Nominal Voltage Details	115v nominal output in battery mode



Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	4 UPS outlets, 4 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(8) 5-15R
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	3 min. (475w)
Half Load Runtime (min.)	10 min. (240w)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 16 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//www.tripplite.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage Correction	Input voltages between 89 and 104 are boosted by 14%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Backlighted LCD screen indicates input voltage, 5-bar battery charge level, overload, AVR, on battery and replace battery status; LCD screen rotates for rack/tower viewing
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; dimmer switch controls LCD brightness
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery status; alarm can be disabled using PowerAlert software
LED Indicators	Front panel LCD display
<b>SURGE / NOISE SUPPRESSION</b>	



UPS AC Suppression Joule Rating	870
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop
Primary Form Factor	Tower
Primary UPS Depth (mm)	183
Primary UPS Height (mm)	300
Primary UPS Width (mm)	94
Shipping Dimensions (hwd / cm)	39.37 x 11.94 x 26.67
Shipping Dimensions (hwd / in.)	15.50 x 4.70 x 10.50
Shipping Weight (kg)	7.48
Shipping Weight (lbs.)	16.50
UPS Housing Material	ABS
UPS Power Module Dimensions (hwd, cm)	29.97 x 9.40 x 18.29
UPS Power Module Dimensions (hwd, in.)	11.8 x 3.7 x 7.2
UPS Power Module Weight (kg)	6.85
UPS Power Module Weight (lbs.)	15.1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	61
Battery Mode BTU / Hr. (Full Load)	485
AC Mode Efficiency Rating (100% Load)	97%
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>
Communications Cable	User supplies USB cable
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp+Lite">http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite</a>



Communications Interface	USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	4 milliseconds (AC to Battery); 3 milliseconds (Battery to AC)
Low Voltage Transfer to Battery Power (Setpoint)	89
High Voltage Transfer to Battery Power (Setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic Voltage Regulation (AVR); Hot swappable batteries; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); ROHS (Restriction of Hazardous Substances)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>