

Power Cord Splitter, C14 to 2x C13 PDU Style - 10A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P004-02M-2C13EU



Allows 2 devices with C14 inlets to share one AC power input cord and one C13 outlet on a PDU or UPS system.

Features

C14-to-C13 Y-Style Splitter Cord Connects 2 Devices with C14 Inlets to One C13 Outlet

This VDE-compliant splitter allows two devices with C14 power inlets to share one AC input cord and one C13 outlet. The P004-02M-2C13EU features an IEC-320-C14 end for connecting to an AC power source and two IEC-320-C13 ends for connecting to devices. By connecting two devices to one outlet, the power cord splitter frees up space in a PDU, UPS system or surge protector and helps reduce cable clutter. The 6.6-foot (2-meter) cable measures 24 inches (610 millimeters) from each C13 connector to the split.

IEC Cable Powers a Wide Variety of Essential Electronics

With this PC power splitter, a single C13 outlet can power two devices, such as computers, monitors, printers, scanners, instrument amplifiers and other equipment compatible with a C13 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this IEC cable is compatible with power and extension cords of all brands.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Specifications

OVERVIEW	
UPC Code	037332280985
Product Type	Splitter
Device Compatibility	Computer; Monitor/HDTV; PDU; Printer; Scanner; UPS
Country/Region	Europe

Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering multiple computers, monitors or other peripherals
- C14 end connects to PDU or UPS power; C13 ends connect to devices' C14 inlets
- Ideal replacement for worn-out or missing C13-to-C14 PDU-style extension cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

Package Includes

P004-02M-2C13EU C14 to C13 Power Cord Splitter, PDU Style, 2 m (6.6 ft.), Black

INPUT	
Maximum Input Amps	10.0
Voltage Compatibility (VAC)	250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.75
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.56
Shipping Weight (kg)	0.25
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.54
Unit Weight (kg)	0.24
ENVIRONMENTAL	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	(2) IEC-320-C13

FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty