

## PDU Power Cord, C13 to C14 - 10A, 250V, H05VV-F, 3 m (9.8 ft.), Black

MODEL NUMBER: P004-03M-EU



Extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 3 m.

### Features

#### C13-to-C14 Power Cord Connects Computers, Printers, Servers and Other Equipment

This durable extension cord is designed for small data centers, office workstations and other lower-amp applications. The power cable can be used to power a computer, server or monitor or to attach a server or drive to a PDU. It can also extend an existing connection up to three meters (9.8 feet) to right-size your current application and allow some flexibility in placing connected equipment.

#### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks and other IT applications in Europe.

### Highlights

- Connects a PC or server to a PDU or UPS system in a data rack or cabinet
- Adds 3 m to your existing power connection to provide flexibility in placing devices
- Fully VDE-compatible for European IT applications
- Ideal replacement for worn-out or missing power cable

### Package Includes

P004-03M-EU C13 to C14 Power Cord, 3 m (9.8 ft.), Black

## Specifications

| OVERVIEW                    |                |
|-----------------------------|----------------|
| UPC Code                    | 037332280893   |
| Product Type                | PDU Power Cord |
| Device Compatibility        | PDU            |
| Country/Region              | Europe         |
| INPUT                       |                |
| Maximum Input Amps          | 10             |
| Voltage Compatibility (VAC) | 250            |
| CONNECTIONS                 |                |
| Side A - Connector 1        | IEC-320-C13    |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                               |
|--------------------------------------|-------------------------------|
| Side B - Connector 1                 | IEC-320-C14                   |
| <b>PHYSICAL</b>                      |                               |
| Plug Color                           | Black                         |
| Cable Jacket Color                   | Black                         |
| Cable Jacket Material                | PVC                           |
| Power Cord Jacket Type               | H05VV-F                       |
| Cable Outer Diameter (OD)            | 6.7 mm                        |
| Number of Conductors                 | 3                             |
| Conductor Gauge                      | 24/0.20AS                     |
| Wire Gauge (AWG)                     | 18                            |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.75                          |
| Power Cord Color                     | Black                         |
| Cable Length (ft.)                   | 9.84                          |
| Cable Length (m)                     | 3.00                          |
| Cable Length (cm)                    | 300                           |
| Shipping Dimensions (hwd / in.)      | 10.00 x 7.99 x 0.50           |
| Shipping Dimensions (hwd / cm)       | 25.40 x 20.29 x 1.27          |
| Shipping Weight (lbs.)               | 0.54                          |
| Shipping Weight (kg)                 | 0.24                          |
| Unit Dimensions (hwd / in.)          | 10.000 x 7.990 x 0.500        |
| Unit Packaging Type                  | Polybag                       |
| Unit Weight (lbs.)                   | 0.54                          |
| Unit Weight (kg)                     | 0.24                          |
| <b>ENVIRONMENTAL</b>                 |                               |
| Operating Temperature Range          | 5° to 158° F (-15° to 70° C)  |
| Storage Temperature Range            | 5° to 140° F (-15° to 60° C)  |
| Operating Humidity Range             | 20% TO 80% RH, NON-CONDENSING |
| Storage Humidity Range               | 20% TO 80% RH, NON-CONDENSING |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                               |
| Antibacterial                        | No                            |
| Armored Cable                        | No                            |
| Angled Plug                          | No                            |
| High Voltage                         | Yes                           |
| Locking Plug                         | No                            |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                |
|-------------------------------------|--------------------------------|
| Coiled Power Cord                   | No                             |
| Locking                             | No                             |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                |
| Product Compliance                  | CE (Europe); REACH; RoHS; UKCA |
| <b>WARRANTY &amp; SUPPORT</b>       |                                |
| Product Warranty Period (Worldwide) | Lifetime limited warranty      |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.