

24 10/100/1000Mbps Port Gigabit L2 Web-Smart Managed PoE+ Switch, 300W, 2 Dedicated Gigabit SFP Slots, 52 Gbps, Web Interface

MODEL NUMBER: NGS24C2POE



Fully managed 24-port web-smart Gigabit 300W PoE+ network switch with dual SFP slots in a 1U rack-mount/desktop unit. Ideal for monitoring and controlling a LAN in a small-to-medium distributed network.

Description

The energy-efficient NGS24C2POE 24-Port Gigabit L2 Web-Smart Managed PoE+ Network Switch features 24 twisted-pair RJ45 Gigabit Ethernet ports that support auto-negotiable 10/100/1000 Mbps and auto MDI/MDIX cross-over detection functions for convenient plug-and-play capability. Each port can be configured to supply up to 30W of PoE+ (Power over Ethernet) via network cable to connected high-wattage devices, such as VoIP phones, wireless access points and security cameras. Two dedicated mini-GBIC SFP ports are also included for uplinking data to other switches via optical fiber or copper.

Easy-to-read LEDs indicate connection and activity status for each port. Built-in web-smart management software gives you remote access to monitor and control each connected device via secure web-based interface. Each port supports up to 2 Gbps with full duplex.

The heavy-duty metal housing mounts into 1U of an EIA-standard 19-inch rack using the included brackets and user-supplied hardware. Or attach the included rubber feet to the bottom of the unit for installation on a flat desktop surface. The five-foot input cord with NEMA 5-15P plug connects to a protected UPS, generator or mains input AC source.

Features

Enterprise Managed Network Switch

- 24 twisted-pair RJ45 Gigabit Ethernet ports for connecting data-intensive devices
- Auto-negotiable 10/100/1000 Mbps
- Automatic MDI/MDIX cross-over detection
- 52 Gbps switching capacity (2 Gbps per port with full duplex)

Highlights

- IP-MAC-Port-Binding, ACL, Storm Control
- Port Security, DHCP Snooping, 802.1x, L2
- Web-Smart management interface, SNMP, RMON features
- Enterprise-level, security and layer 2 management
- Cost-effective form factor for small and medium businesses

Package Includes

- NGS24C2POE 24-Port Gigabit L2 Web-Smart Managed PoE+ Network Switch
- Detachable AC power cord w/NEMA 5-15P plug, 5 ft.
- (2) Rack-mounting brackets
- (8) Screws
- (4) Rubber feet
- Owner's manual



- Easy-to-read LEDs indicate connection and activity status for each port
- Supports 9k jumbo frames
- Supports MAC address auto-learning and auto-aging up to 8,000 addresses
- Advanced Enterprise-level and L2 management features

300W Total PoE+ Budget

- Each RJ45 port can be configured to supply in-line power to connected devices, such as VoIP phones, wireless access points and security cameras
- 30W maximum per port

Built-In Web-Smart Management Software

- Remote access allows monitoring and control of connected equipment via simple Web interface
- VLAN, trunking, VPN, port monitoring and other features improve network efficiency and performance

Dual Dedicated Mini-GBIC SFP Ports

- Connect to Mini-GBIC SFP modules for uplinking to other switches via optical fiber or copper
- LEDs indicate interface traffic

Compliant with IEEE Standards

- Meets IEEE 802.3ab, 802.3i, 802.3u, 802.3x, 802.3, 802.1q, 802.1p, 802.3af and 802.3at standards

Versatile Installation Options

- Fanless metal housing mounts in 1U of EIA-standard 19 in. racks
- Supports desktop installation using included rubber feet on flat surface
- 5 ft. power cord with NEMA 5-15P plug connects to compatible AC power source

Specifications

| OVERVIEW | |
|-----------------------------|-----------------------------|
| UPC Code | 037332194862 |
| Product Type | Network Switch |
| INPUT | |
| Electrical Consumption | 450 watts max. |
| Input Plug Features | Detachable input cord |
| Voltage Compatibility (VAC) | 100; 110; 120; 127; 208/240 |
| Input Phase | Single-Phase |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 5 |



| | |
|--|--|
| Input Cord Length (m) | 1.52 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | 1 included switch enables factory reset |
| LED Indicators | Power LED (Red); One connection/activity LED per RJ-45 port (Amber indicates 10/100Mbps link; Green indicates 1000Mbps link; LEDs flash to indicate port activity); One POE port per RJ-45 port (Green when POE is active; Blinks when port is overloaded); Two LEDs indicate SFP connection (Green) |
| PHYSICAL | |
| Color | Black |
| Minimum Required Rack Depth (cm) | 20.80 |
| Minimum Required Rack Depth (inches) | 8.19 |
| Primary Form Factor | Desktop; Rackmount |
| Shipping Dimensions (hwd / cm) | 8.79 x 55.50 x 29.49 |
| Shipping Dimensions (hwd / in.) | 3.46 x 21.85 x 11.61 |
| Shipping Weight (kg) | 3.95 |
| Shipping Weight (lbs.) | 8.71 |
| Unit Dimensions (hwd / cm) | 4.39 x 43.99 x 20.8 |
| Unit Dimensions (hwd / in.) | 1.73 x 17.32 x 8.19 |
| Unit Weight (kg) | 3.10 |
| Unit Weight (lbs.) | 6.84 |
| ENVIRONMENTAL | |
| Storage Temperature Range | -40 to 158 F (-40 to 70 C) |
| Relative Humidity | 10 to 90% (Non-condensing) |
| Operating Temperature | 32 to 104 F (0 to 40 C) |
| Power Consumption (Watts) | 450 |
| CONNECTIONS | |
| Ports | 26 |
| Network Switch Ports | (24) 10/100/1000 (RJ45); (2) Dedicated SFP |
| STANDARDS & COMPLIANCE | |
| Certifications | Compliant standards: IEEE 802.3ab (1000BASE-T GIGABIT ETHERNET), IEEE 802.3i (10BASE-T ETHERNET), IEEE 802.3u (100BASE-T ETHERNET), IEEE 802.3x (FULL DUPLEX/FLOW CONTROL), IEEE 802.3 (NWAY AUTO-NEGOTIATION), 802.1q (TAGGED VLAN), 802.1p (QUALITY OF SERVICE), 802.af (POE), 802.at (POE+) |
| Approvals | Tested to: UL 60950-1:2007 (2nd Ed); CAN/CSA C22.2 NO. 60950-1-07 2nd Edition, 2014-10; FCC Class A (Emissions) |
| WARRANTY | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|-------------------------|
| Product Warranty Period (Worldwide) | 5-year limited warranty |
|--|-------------------------|

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>