

M12 X-Code Cat6a 10G F/UTP CMR-LP Shielded Ethernet Cable (Right-Angle M/M), IP68, PoE, Blue, 3 m (9.8 ft.)

MODEL NUMBER: NM12-6A3-03M-BL



Connects 10G Ethernet network equipment in industrial and other harsh environments subject to vibration, humidity and extreme temperatures.

Features

Cat6a M12 Cable Recommended for Industrial and Other Harsh Environments

This M12 X-Code cable connects 10 GbE networks in wet/humid environments, places subject to vibration and other areas where protection from harsh elements is essential, such as factories, warehouses, recycling plants, airports, railways and machine shops. The circular M12 connectors with 12-millimeter locking thread are especially designed for washdown and corrosive applications, including agriculture, alternative energy, communications, factory automation, measurement and control, robotics, transportation and food/beverage facilities.

IP68 Rating Denotes Resistance to Dust and Water

The IP68 rating means the M12 cable is not only 100% protected against dust, but also able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance.

Supports Power over Ethernet to Save You Money and Give You More Installation Choices

Because this Cat6a cable supports high-power 60W PoE, it can supply the power to operate compatible data, voice, security and audio/video PoE devices, such as surveillance cameras, VoIP telephones and access control devices. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device, as well as installing separate power and data cables. It also helps you install PoE devices in areas far away from AC outlets, such as poles or ceilings.

CMR-LP Certified for Cable Installations with Increased Power Levels

UL's Limited Power (LP) certification indicates the NM12-6A3-03M-BL has been evaluated to handle the marked current under installation scenarios without exceeding the temperature rating of the cable. This CMR-LP-certified cable provides a simple way to prepare installations for increased power levels without having to worry about susceptible issues caused by excessive heat.

Right-Angle Plug Makes Connecting in Tight Spaces Easier

One M12 connector is designed at a space-saving right angle, making it easy to install in confined spaces, such as a crowded equipment rack or a network device located flush against a wall. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Highlights

- Designed to withstand vibration, moisture and extreme temperatures in harsh environments
- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
- Supports 60W PoE to save you expense and effort of powering PoE devices individually
- UL CMR-LP certified to meet high-temperature safety standards in PoE applications
- Right-angle M12 end relieves cable strain and allows easy connection in tight spaces

Package Includes

NM12-6A3-03M-BL M12 X-Code Cat6a 10G Ethernet Cable, M/M, Blue, 3 m (9.8 ft.)



Colored Blue to Avoid Misidentification That Can Cause Costly Downtime

This Cat6a F/UTP copper cable features a blue PVC jacket that allows easy, fast identification in field devices, controllers and switches and helps prevent the cable from becoming inadvertently disconnected.

Specifications

OVERVIEW	
UPC Code	037332265586
Technology	Cat6a; PoE
PHYSICAL	
Cable Jacket Color	Blue
Cable Jacket Material	PVC
Cable Jacket Rating	CMR-LP
Cable Shielding	F/UTP
Cable Outer Diameter (OD)	7.3MM
Conductor Material	Solid Copper
Wire Gauge (AWG)	23
Cable Length (ft.)	9.8
Cable Length (m)	2.99
ENVIRONMENTAL	
Operating Temperature Range	14 to 140°F (-10 to 60°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Operating Humidity Range	0% to 90% RH, NON-CONDENSING
Storage Humidity Range	0% to 90% RH, NON-CONDENSING
Power Provided to Connected Device(s)	51W (60W @ SOURCE, 51W @ DEVICE)
COMMUNICATIONS	
Network Compatibility	10 Gbps
CONNECTIONS	
PoE Capability	60W (802.3bt)
Side A - Connector 1	M12 X CODE (MALE)
Side B - Connector 1	M12 X CODE (MALE)
Crossover Wiring	No
PoE Type	Type 3 PoE++/UPoE (60W, IEEE 802.3bt)



Connector Type	Snagless
FEATURES & SPECIFICATIONS	
IP68 Rated	Yes
Snagless Connector	Yes
Angled Plug	Yes
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH, UL-CMP
Protection Rating	IP68
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>