

# Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 6 ft. (1.83 m), Red

MODEL NUMBER: P005-006-ARD



Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 6 ft.

## Features

**C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime** This computer power extension cord features a red SJT jacket and fully molded red ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

## Specifications

| OVERVIEW                    |   |
|-----------------------------|---|
| UPC Code                    | 037332199058  |
| Device Compatibility        | Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU |
| Country/Region              | Global  |
| INPUT                       |   |
| Maximum Input Amps          | 15  |
| Voltage Compatibility (VAC) | 100-250   |
| CONNECTIONS                 |   |
| Side A - Connector 1        | IEC-320-C14   |

## Highlights

- Recommended for powering computers, servers and other network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Color-coded red for fast, easy identification in a crowded rack or workstation
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

## Applications

- Connect devices like computers, servers and monitors to a PDU up to 6-ft. (1.83 m) away in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

## Package Includes

- P005-006 Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 6-ft. (1.83 m), Red



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Side B - Connector 1                 | IEC-320-C13                         |
| <b>PHYSICAL</b>                      |                                     |
| Plug Color                           | Red                                 |
| Cable Jacket Color                   | Red                                 |
| Cable Jacket Material                | PVC                                 |
| Cable Jacket Rating                  | VW-1                                |
| Power Cord Jacket Type               | SJT                                 |
| Cable Outer Diameter (OD)            | 9.3mm                               |
| Number of Conductors                 | 3                                   |
| Wire Gauge (AWG)                     | 14                                  |
| Wire Gauge (OD - mm <sup>2</sup> )   | 2.08                                |
| Cable Length (ft.)                   | 6                                   |
| Cable Length (m)                     | 1.83                                |
| Cable Length (cm)                    | 182.88                              |
| Shipping Dimensions (hwd / in.)      | 9.90 x 7.00 x 0.50                  |
| Shipping Dimensions (hwd / cm)       | 25.15 x 17.78 x 1.27                |
| Shipping Weight (lbs.)               | 0.65                                |
| Shipping Weight (kg)                 | 0.29                                |
| <b>ENVIRONMENTAL</b>                 |                                     |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C)         |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C)         |
| Operating Humidity Range             | 10% to 65% RH                       |
| Storage Humidity Range               | 10% to 65% RH                       |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| Antibacterial                        | No                                  |
| Angled Plug                          | No                                  |
| High Voltage                         | Yes                                 |
| Locking Plug                         | No                                  |
| Coiled Power Cord                    | No                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                     |
| Product Certifications               | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                   | RoHS; REACH                         |
| <b>WARRANTY &amp; SUPPORT</b>        |                                     |



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |                           |
|--|---------------------------|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |
|--|---------------------------|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.