

## Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 15A, 125V, 14 AWG, 25 ft. (7.62 m), Black

MODEL NUMBER: P006-025-HG15



Hospital-grade power cord connects a computer, monitor or other peripheral to a hospital-grade AC outlet in a medical facility.

### Features

**Hospital-Grade Power Cable is a Safe Solution for Medical Facilities** This hospital-grade IEC power cord features 14 AWG wire suitable for high power connections, making it a reliable solution for devices that require a higher-rated, heavier-gauge cable. The C13 end connects to a computer, mobile cart, printer, scanner, monitor or other compatible hospital component with a three-pin C14 inlet. The NEMA 5-15P-HG green-dot plug connects to a hospital-grade AC power source located outside patient-care vicinities. The 25-ft. (7.62 m) length allows you great flexibility in placing equipment with respect to the power outlet.

**Designed and Tested to Strict Hospital-Grade Standards** This hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

## Specifications

OVERVIEW	
UPC Code	037332193315
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125

### Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- 25-ft. (7.62 m) length allows great flexibility in placing devices in relationship to AC outlet
- Medical power cord replaces or upgrades power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

### Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 25-ft. (7.62 m) away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 25-ft. (7.62 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P006-025-HG15 NEMA 5-15P to C13 Computer Power Cable, 25-ft. (7.62 m), Black

<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	25
Cable Length (m)	7.62
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	IEC-320-C13
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed

Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty