



Powering Business Worldwide

End-of-Row Doors for RapidPod Aisle Containment System - Dual Slide, 96”H x 48”W, TAA

MODEL NUMBER: NXEORDDS9648



Block escape routes for air and eliminate air recirculation and mixing in your modular RapidPod Aisle Containment System.

Features

Modular Customization of Your RapidPod Aisle Containment System

These end-of-row doors (EoRD) optimize airflow management in your RapidPod® Aisle Containment System by sealing off key air escape routes, which reduces air recirculation and air mixing. This allows for higher ambient temperatures, which lowers your energy costs and extends the life of the valuable equipment in your high-performance data center. All essential components are included with no upgrades needed.

Designed for Convenience and Durability

The space-saving dual-slide doors are easy to install, which means very little downtime and disruption in your active data center. Their field-reversible design supports both left-hand and right-hand sliding configurations for convenient installation options. Also included are ceiling-mount provisions for threaded rod installation, ensuring secure overhead support.

A Practical, High-Performance Solution for Aisle Containment

The fully transparent and impact-resistance windows boast a stringent UL94 V-0 rating for the utmost safety and visibility. The automatic-close/hold-open feature allows smooth, reliable operation. The sliding doors don't obstruct open aisles, maintaining optimal traffic flow. An integrated edge grip seal at the bottom of the doors seals air gaps to maintain blockage.

TAA-Compliant for GSA Schedule Purchases

The NXEORDDS9648 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Field-reversible design supports both left- and right-hand sliding configurations
- Fast, hassle-free installation minimizes downtime and disruption in a busy data center
- Fully transparent, impact-resistance windows rated UL94 V-0 for safety and visibility
- Automatic-close/hold-open feature ensures smooth and reliable operation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

End-of-row doors, dual slide, 96 x 48 in.

Specifications

OVERVIEW

UPC Code

037332301130



Powering Business Worldwide

Aisle Containment System Component Type	Door Kit
PHYSICAL	
Color	Black; Gray
Unit Dimensions (hwd / in.)	96.000 x 48.000 x 6.000
Unit Dimensions (hwd / cm)	96H 48W
Unit Weight (lbs.)	50
Unit Weight (kg)	22.68
Rack Compatibility	300 mm (In-Row Cooler); 600 mm (Standard); 750 mm (Wide)
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.