

OMNISMART1050PNP is not for sale in Colorado, Vermont and Washington state. Customers in these states should purchase the recommended ENERGY STAR® 2.0 model instead: ECO1500LCD. Learn more about [ENERGY STAR 2.0 and sales restrictions](#) in these states.

OmniSmart 120V 1050VA 705W Line-Interactive UPS, Tower, USB port

MODEL NUMBER: **OMNISMART1050**



Highlights

- 1050VA / 1.05kVA tower 120V line interactive UPS
- Corrects brownouts and overvoltages from 75V to 147V
- USB port, Front panel status LEDs
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

Package Includes

- OMNI SMART 1050 UPS System
- USB cable
- Warranty information
- Instruction manual

Description

Tripp Lite's OMNI SMART 1050 line interactive UPS system offers voltage regulation, surge suppression and long lasting battery support for personal computers, internetworking equipment and other sensitive electronics. Supports a single entry level PC system for up to 60 minutes during power failures to facilitate a safe shutdown without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 75 volts and overvoltages to 147 volts back to normal 120V levels, all without using battery power. Includes 6 battery supported outlets and 6-ft. (1.83 m) AC line cord. USB port enables optional safe unattended system shutdown in the case of extended power failure as well as continuous UPS and site power condition monitoring, USB cable included. PowerAlert software available via free download. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and overload. 1050VA / 705 watt power handling ability supports multiple entry-level PCs, network workstations, point-of-sale terminals, small to medium business phone systems, audio/video workstations and heavily configured home theater systems. Offers 7 minutes battery runtime with a full load of 1050VA and 23 minutes with a half load of 525VA. Supports hot swap battery replacement via built-in access panel. \$200,000 connected equipment insurance (U.S., Canada, and Puerto Rico only).

Features

- OMNISMART1050 line interactive UPS system offers voltage regulation and battery support, plus complete AC surge suppression
- Prevents equipment damage, data loss and downtime due to power problems
- Supports a single entry level PC system for up to 60 minutes during power failures to enable a safe system shutdown
- Supports a max load of 1050VA for 7 minutes
- Supports a half load of 525VA for 23 minutes

- Automatic Voltage Regulation (AVR) circuits correct brownouts as low as 75 and overvoltages as high as 147 volts to normal 120 volt levels without using battery power
- Upright tower configuration uses only 51 square inches of floor or desktop space
- Includes 6 battery supported outlets, 6-ft. (1.83 m) AC line cord (all NEMA 5-15)
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again
- Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and overload status
- 1050VA / 705 watt power handling ability supports multiple entry-level PCs, network workstations, point-of-sale terminals, small to medium business phone systems, audio/video equipment stations and heavily configured home theater systems
- Supports hot-swap battery replacement via built-in battery access panel
- Compatible with 120V / 60Hz applications for USA, Canada, Mexico and more
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332033796
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	6.7A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	1050
Output Capacity (kVA)	1.05
Output Watt Capacity (Watts)	705
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz

EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	480
AC Suppression Response Time	Instantaneous
PHYSICAL	
Primary Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary UPS Depth (mm)	183
Primary UPS Height (mm)	292
Primary UPS Width (mm)	173
Shipping Dimensions (hwd / in.)	15.60 x 10.60 x 10.50
Shipping Dimensions (hwd / cm)	39.62 x 26.92 x 26.67
Shipping Weight (lbs.)	30.50
Shipping Weight (kg)	13.83
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	29.21 x 17.27 x 18.29
UPS Power Module Dimensions (hwd, in.)	11.5 x 6.8 x 7.2
UPS Power Module Weight (kg)	13.15
UPS Power Module Weight (lbs.)	29
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	74
Battery Mode BTU / Hr. (Full Load)	564
AC Mode Efficiency Rating (100% Load)	94%
COMMUNICATIONS	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at https://www.tripplite.com/poweralert
Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications

Network Management Card Description	Network management not supported
Communications Interface	USB
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 Ultimate Lifetime Insurance