

## Laptop Power Cord Adapter, C14 to C5 - 2.5A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P014-02M-EU



Connects your notebook computer or laptop with a 3-slot C6 power inlet to a PDU or UPS system.

### Features

#### Laptop Power Adapter Cord Connects Notebook Computers to an AC Outlet

This VDE-compliant power cable connects a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other power source with a C13 outlet. The P014-02M-EU features an IEC-320-C14 end for connecting to an AC power source and an IEC-320-C5 end for connecting to devices. The 6.6-foot (2-meter) cable allows you welcome flexibility in placing equipment with respect to the power outlet.

#### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm2 enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

## Specifications

OVERVIEW	
UPC Code	037332280992
Product Type	Laptop Power Cord
Device Compatibility	Laptop; Monitor/HDTV
Country/Region	Europe; UK
INPUT	
Maximum Input Amps	2.5
Voltage Compatibility (VAC)	250
PHYSICAL	

### Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- 2-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable
- VDE-compliant H05VV-F jacket allows use in European IT applications

### Package Includes

P014-02M-EU C14 to C5 Laptop Power Cord Adapter, 2 m (6.6 ft.), Black

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.75
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Shipping Dimensions (hwd / in.)	9.02 x 7.01 x 0.50
Shipping Dimensions (hwd / cm)	22.91 x 17.81 x 1.27
Shipping Weight (lbs.)	0.38
Shipping Weight (kg)	0.17
Unit Dimensions (hwd / in.)	9.020 x 7.010 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.36
Unit Weight (kg)	0.16
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Relative Humidity	10 ~ 65% RH, Non-Condensing
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C5
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Armored Cable	No
Angled Plug	No

High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty