

Laptop Power Cord Adapter, C14 to C5 - 2.5A, 250V, H05VV-F, 0.15 m (6 in.), Black

MODEL NUMBER: P014-P15M-EU



Connects your notebook computer or laptop with a 3-slot C6 power inlet to a PDU or UPS system.

Features

Laptop Power Adapter Cord Connects Notebook Computers to an AC Outlet

This VDE-compliant power cable connects a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other power source with a C13 outlet. The P014-P15M-EU features an IEC-320-C14 end for connecting to an AC power source and an IEC-320-C5 end for connecting to devices.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Specifications

OVERVIEW	
UPC Code	037332281005
Product Type	Laptop Power Cord
Device Compatibility	Laptop; Monitor/HDTV
Country/Region	Europe; UK
INPUT	
Maximum Input Amps	2.5
Voltage Compatibility (VAC)	250
PHYSICAL	

Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- Ideal replacement for a worn-out or missing laptop adapter power cable
- VDE-compliant H05VV-F jacket allows use in European IT applications

Package Includes

P014-P15M-EU C14 to C5 Laptop Power Cord Adapter, 0.15 m (6 in.), Black

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.75
Power Cord Color	Black
Cable Length (ft.)	0.49
Cable Length (m)	0.15
Shipping Dimensions (hwd / in.)	5.00 x 4.02 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.21 x 1.27
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	5.000 x 4.020 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.10
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	5° to 158°F (-15° to 70°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	10 ~ 65% RH, Non-Condensing
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C5
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No

High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty