

# Laptop Power Cord Adapter, C14 to C5 - 2.5A, 250V, H05VV-F, 0.15 m (6 in.), Black

MODEL NUMBER: P014-P15M-EU



Connects your notebook computer or laptop with a 3-slot C6 power inlet to a PDU or UPS system.

## Features

### Laptop Power Adapter Cord Connects Notebook Computers to an AC Outlet

This VDE-compliant power cable connects a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other power source with a C13 outlet. The P014-P15M-EU features an IEC-320-C14 end for connecting to an AC power source and an IEC-320-C5 end for connecting to devices.

### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

## Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- Ideal replacement for a worn-out or missing laptop adapter power cable
- VDE-compliant H05VV-F jacket allows use in European IT applications

## Package Includes

P014-P15M-EU C14 to C5 Laptop Power Cord Adapter, 0.15 m (6 in.), Black

# Specifications

OVERVIEW	
UPC Code	037332281005
Product Type	Laptop Power Cord
Device Compatibility	Laptop; Monitor/HDTV
Country/Region	Europe; UK
INPUT	
Maximum Input Amps	2.5
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	IEC-320-C5
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.75
Power Cord Color	Black
Cable Length (ft.)	0.49
Cable Length (m)	0.15
Shipping Dimensions (hwd / in.)	5.00 x 4.02 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.21 x 1.27
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	5.000 x 4.020 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.10
Unit Weight (kg)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5° to 158°F (-15° to 70°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	10 ~ 65% RH, Non-Condensing
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.