

# Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P018-002



Heavy-duty C14 to C15 power cord connects a PoE network switch or other device with a C16 power inlet to a PDU or UPS system.

## Features

**C15 to C14 Power Cord for Network Devices That Require a Heavy-Gauge Connection** This 250V C15 to C14 cable features 14 AWG wire suitable for high power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as electric kettles, PoE (Power over Ethernet) switches with high-wattage power supplies, and similar network components. This IEC C14 to IEC C15 cord can also replace or upgrade the standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

## Highlights

- Recommended for powering PoE switches with high-wattage power supplies
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- C14 to C15 power cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

## Applications

- Connect devices like high-wattage PoE switches to a PDU up to 2-ft. (0.61 m) away in your data center
- Update or replace the standard power cord provided by a device's original manufacturer
- Extend an existing power connection by 2-ft. (0.61 m)

## Package Includes

- P018-002 IEC C14 to IEC C15 Power Cable, 2-ft. (0.61 m), Black

## Specifications

OVERVIEW	
UPC Code	037332182555
Device Compatibility	Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15



Powering Business Worldwide

TRIPP LITE  
SERIES

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	0.50 x 3.00 x 4.00
Shipping Dimensions (hwd / cm)	1.27 x 7.62 x 10.16
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.