


## Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 10 ft. (3.1 m), Yellow

MODEL NUMBER: P018-010-AYW



Connects a PoE network switch or server with a C16 power inlet to a PDU or UPS system with C13 outlets.

### Features

#### C15 to C14 Power Cord for Network Devices That Require a Heavy-Gauge Connection

This 250V power cable features 14 AWG wire suitable for high-power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as PoE (Power over Ethernet) switches with high-wattage power supplies and similar network components. This cord can also replace or upgrade the standard power cord provided by the device's manufacturer.

#### Yellow Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The UL-listed cable has a yellow SJT jacket, which is easy to identify quickly in a crowded PDU or UPS system and helps prevent the cable from becoming accidentally disconnected.

### Highlights

- Recommended for powering PoE switches with high-wattage power supplies
- 10 ft. length allows flexibility in placing devices while avoiding cable clutter
- Ideal replacement or upgrade from the original manufacturer's power cord
- Yellow jacket permits fast, easy identification in a crowded rack
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Package Includes

P018-010-AYW C14 to C15 Power Cable, 10 ft. (3.1 m), Yellow

## Specifications

OVERVIEW	
UPC Code	037332284396
Device Compatibility	Network Switch; PDU; Server; UPS
Country/Region	North America
INPUT	
Maximum Input Amps	15.0
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	IEC-320-C15
<b>PHYSICAL</b>	
Color	Yellow
Plug Color	Yellow
Cable Jacket Color	Yellow
Connector Color	Yellow
Cable Jacket Material	PVC
Cable Jacket Rating	SJT
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	10.98 x 7.01 x 0.50
Shipping Weight (kg)	0.43
Unit Dimensions (hwd / in.)	10.980 x 7.010 x 0.500
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% TO 65% RH, NON-CONDENSING
Storage Humidity Range	10% TO 65% RH, NON-CONDENSING
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL Listed; cUL Listed
Product Compliance	RoHS



Powering Business Worldwide

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.