


Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 10 ft. (3.1 m), Yellow

MODEL NUMBER: P018-010-AYW



Connects a PoE network switch or server with a C16 power inlet to a PDU or UPS system with C13 outlets.

Features

C15 to C14 Power Cord for Network Devices That Require a Heavy-Gauge Connection

This 250V power cable features 14 AWG wire suitable for high-power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as PoE (Power over Ethernet) switches with high-wattage power supplies and similar network components. This cord can also replace or upgrade the standard power cord provided by the device's manufacturer.

Yellow Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The UL-listed cable has a yellow SJT jacket, which is easy to identify quickly in a crowded PDU or UPS system and helps prevent the cable from becoming accidentally disconnected.

Highlights

- Recommended for powering PoE switches with high-wattage power supplies
- 10 ft. length allows flexibility in placing devices while avoiding cable clutter
- Ideal replacement or upgrade from the original manufacturer's power cord
- Yellow jacket permits fast, easy identification in a crowded rack
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Package Includes

P018-010-AYW C14 to C15 Power Cable, 10 ft. (3.1 m), Yellow

Specifications

| OVERVIEW | |
|-----------------------------|----------------------------------|
| UPC Code | 037332284396 |
| Device Compatibility | Network Switch; PDU; Server; UPS |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 15.0 |
| Voltage Compatibility (VAC) | 100-250 |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C14 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|-------------------------------|
| Side B - Connector 1 | IEC-320-C15 |
| PHYSICAL | |
| Color | Yellow |
| Plug Color | Yellow |
| Cable Jacket Color | Yellow |
| Connector Color | Yellow |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | SJT |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 9.3mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 14 |
| Wire Gauge (OD - mm ²) | 2.08 |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| Cable Length (in.) | 120 |
| Shipping Dimensions (hwd / in.) | 10.98 x 7.01 x 0.50 |
| Shipping Weight (kg) | 0.43 |
| Unit Dimensions (hwd / in.) | 10.980 x 7.010 x 0.500 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 10% TO 65% RH, NON-CONDENSING |
| Storage Humidity Range | 10% TO 65% RH, NON-CONDENSING |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | No |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | UL Listed; cUL Listed |
| Product Compliance | RoHS |

WARRANTY & SUPPORT

| | |
|--|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
|--|---------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.