

Power Extension Cord, C20 to C13 - 10A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P032-02M-EU



Connects a server or PC with a C14 inlet to a PDU or UPS with C19 outlets.

Features

Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a computer, server, router or other device with a C14 power inlet to a PDU, UPS system or surge protector with C19 outlets. It can also extend an existing power connection up to two meters (6.6 feet). The P032-02M-EU features an IEC-320-C20 end for connecting to an AC power source or cord and an IEC-320-C13 end for connecting to a data center device.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Specifications

OVERVIEW	
UPC Code	037332281012
Product Type	Power Extension Cord
Device Compatibility	Computer; PDU; UPS
Country/Region	Europe; UK
INPUT	
Maximum Input Amps	10.0
Voltage Compatibility (VAC)	250
PHYSICAL	

Highlights

- Recommended for powering computers, servers, routers and other network devices
- 2-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing power extension cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

Package Includes

P032-02M-EU C20 to C13
Extension Power Cable, 2 m (6.6 ft.), Black

Plug Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	8.2 mm
Number of Conductors	3
Conductor Gauge	48/0.2AS
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.5
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Cable Length (cm)	200
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.62
Shipping Weight (kg)	0.28
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.419
Unit Weight (kg)	0.19
ENVIRONMENTAL	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes

Locking Plug	No
Coiled Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty