

## Power Extension Cord, C19 to Right Angle C20 - Heavy Duty, 20A, 250V, 12 AWG, 2 ft., Black

MODEL NUMBER: P036-002-20RA



Heavy-duty extension cable with right-angle C20 end allows connection of C19/C20 high-output devices in tight spaces or awkward angles.

### Features

**20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The two-foot length helps reduce cable clutter and minimize the risk of tripping.

**Right-Angle C20 Plug Makes Connecting in Tight Spaces Easier** The C19 to C20 right-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C20 plug guides the heavy-duty extension cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

## Specifications

### Highlights

- Right-angle C20 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering servers, routers and other high-output network devices
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 2 ft. away in your data center
- Extend an existing power connection up to 2 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

### Package Includes

- P036-002-20RA C19 to Right-Angle C20 Heavy-Duty Extension Cord, 2 ft., Black



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>OVERVIEW</b>	
UPC Code	037332156532
Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	20
Cable Length (ft.)	2
Cable Length (m)	0.6
Voltage Compatibility (VAC)	100-250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	1.27 x 12.70 x 19.30
Shipping Dimensions (hwd / in.)	0.50 x 5.00 x 7.60
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.50
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C20 - RIGHT ANGLE
Side B - Connector 1	IEC-320-C19
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>