

# Power Extension Cord, Right-Angle C13 to C14 PDU Style - 10A, 250V, 18 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P004-002-13RA



Computer power extension cord with right-angle C13 plug allows connection of a PC, printer or monitor in tight spaces or awkward angles.

## Features

**C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment** This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 2-ft. (0.61 m). The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

**Right-Angle C13 Plug Makes Connecting in Tight Spaces Easier** The C13 to C14 right-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C13 plug guides the computer power supply cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

## Highlights

- Right-angle C13 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering computers, printers and other essential peripherals
- Adds 2-ft. (0.61 m) to your existing power connection to provide flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

## Applications

- Connect devices like computers, servers and monitors to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord
- Power a device located in a hard-to-access area behind a desk or flush against a wall

## Package Includes

- P004-002-13RA C14 Male to C13 Female Power Cable, 2-ft. (0.61 m), Black

## Specifications

OVERVIEW	
UPC Code	037332156419
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13 - RIGHT ANGLE
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	Yes
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
----------------------------------------	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.