

PDU Power Cord, C13 to C14 - 10A, 250V, H05VV-F, 4 m (13.1 ft.), Black

MODEL NUMBER: P004-04M-EU



Extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 4 m.

Features

C13-to-C14 Power Cord Connects Computers, Printers, Servers and Other Equipment

This durable extension cord is designed for small data centers, office workstations and other lower-amp applications. The power cable can be used to power a computer, server or monitor or to attach a server or drive to a PDU. It can also extend an existing connection up to four meters (13.1 feet) to right-size your current application and allow some flexibility in placing connected equipment.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks and other IT applications in Europe.

Highlights

- Connects a PC or server to a PDU or UPS system in a data rack or cabinet
- Adds 4 m to your existing power connection to provide flexibility in placing devices
- Fully VDE-compatible for European IT applications
- Ideal replacement for worn-out or missing power cable

Package Includes

P004-04M-EU C13 to C14 Power Cord, 4 m (13.1 ft.), Black

Specifications

OVERVIEW	
UPC Code	037332281203
Product Type	PDU Power Cord
Device Compatibility	PDU
Country/Region	Europe
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	IEC-320-C13



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C14
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.75
Power Cord Color	Black
Cable Length (ft.)	13.12
Cable Length (m)	4.00
Cable Length (cm)	400
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.78
Shipping Weight (kg)	0.35
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.78
Unit Weight (kg)	0.35
ENVIRONMENTAL	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No



Powering Business Worldwide

TRIPP LITE
SERIES

Coiled Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.