

## Power Extension Cord, C19 to C20 - 16A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P036-02M-EU



Connects high-output devices with C19/C20 power connectors, including routers and blade servers.

### Features

#### Power Cord Connects High-Output Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a router, blade server or other high-output network device with a C20 power inlet to a PDU, UPS system or surge protector with C19 outlets. It can also extend an existing power connection up to two meters (6.6 feet). The P036-02M-EU features an IEC-320-C20 end for connecting to an AC power source or cord and an IEC-320-C19 end for connecting to a blade server chassis or other high-output device.

#### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

## Specifications

OVERVIEW	
UPC Code	037332281029
Product Type	Power Extension Cord
Device Compatibility	Network Switch; PDU; Router; Server; UPS
Country/Region	Europe
INPUT	
Maximum Input Amps	16
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	IEC-320-C20

### Highlights

- Recommended for powering blade server chassis and other high-output devices
- 2-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing power extension cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

### Package Includes

P036-02M-EU C19 to C20 Power Extension Cord, 2 m (6.6 ft.), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	IEC-320-C19
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	8.2 mm
Number of Conductors	3
Conductor Gauge	48/0.2AS
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.5
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.64
Shipping Weight (kg)	0.29
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.399
Unit Weight (kg)	0.18
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5° to 158°F (-15° to 70°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE  
SERIES

STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.