

## Heavy Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 2 ft., Orange

MODEL NUMBER: P005-002-AOR



Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 2 ft.

### Features

**C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The two-foot length helps reduce cable clutter and minimize the risk of tripping.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime** This computer power extension cord features an orange SJT jacket and fully molded orange ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

### Highlights

- Recommended for powering computers, servers and other network devices
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Color-coded orange for fast, easy identification in a crowded rack or workstation
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 2 ft. away in your data center
- Extend an existing power connection up to 2 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P005-002-AOR Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 2 ft., Orange

## Specifications

### OVERVIEW



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

UPC Code	037332199393
Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	15
Cable Length (ft.)	2
Cable Length (m)	0.6
Cable Length (in.)	24
Voltage Compatibility (VAC)	250
Cable Length (cm)	60.96
<b>PHYSICAL</b>	
Color	Orange
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50
Shipping Weight (kg)	0.15
Shipping Weight (lbs.)	0.33
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>