

**Important Note**

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

**Power Extension Cord, Locking C19 to C20 - Heavy-Duty, 20A, 100-250V, 12 AWG, 6 ft. (1.83 m), Black**

MODEL NUMBER: P036-L06



C20 to C19 cord powers a server, router, switch, blade server enclosure or other network device that requires a heavy-gauge cable.

**Features**

**C20 to C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This rugged cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a server, router, switch, blade server enclosure or other network device to a UPS system or PDU. It is also an ideal replacement or upgrade from the standard power cord provided by the device's manufacturer. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

**Locking C19 Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C19 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

**Lifetime Warranty** The P036-L06 is backed by a lifetime warranty, ensuring reliability and performance.

**Specifications**

| OVERVIEW             |  |
|----------------------|--|
| UPC Code             | 037332218315                             |
| Device Compatibility | Server; Router; Network Switch; UPS; PDU |
| Country/Region       | North America                            |

**Highlights**

- Recommended for powering network devices that require heavy-gauge cabling
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Reliable replacement or upgrade from standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking C19 connector maintains secure link to avoid loss of power and costly downtime

**Applications**

- Connect devices like servers, routers and network switches to a UPS system up to 6-ft. (1.83 m) away in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

**Package Includes**

- P036-L06 C20 to C19 Power Cable, Locking C19 Connector, 6-ft. (1.83 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

| INPUT                              |                              |
|------------------------------------|------------------------------|
| Maximum Input Amps                 | 20                           |
| Voltage Compatibility (VAC)        | 100-250                      |
| CONNECTIONS                        |                              |
| Side A - Connector 1               | IEC-320-C20                  |
| Side B - Connector 1               | IEC-320-C19 - LOCKING        |
| PHYSICAL                           |                              |
| Plug Color                         | Black                        |
| Cable Jacket Color                 | Black                        |
| Cable Jacket Material              | PVC                          |
| Cable Jacket Rating                | VW-1                         |
| Power Cord Jacket Type             | SJT                          |
| Cable Outer Diameter (OD)          | 10.8mm                       |
| Number of Conductors               | 3                            |
| Wire Gauge (AWG)                   | 12                           |
| Wire Gauge (OD - mm <sup>2</sup> ) | 3.31                         |
| Cable Length (ft.)                 | 6                            |
| Cable Length (m)                   | 1.83                         |
| Shipping Dimensions (hwd / in.)    | 12.80 x 8.59 x 0.50          |
| Shipping Dimensions (hwd / cm)     | 32.51 x 21.82 x 1.27         |
| Shipping Weight (lbs.)             | 0.98                         |
| Shipping Weight (kg)               | 0.44                         |
| Unit Dimensions (hwd / in.)        | 0.000 x 0.000 x 0.000        |
| ENVIRONMENTAL                      |                              |
| Operating Temperature Range        | -4° to 221°F (-20° to 105°C) |
| Storage Temperature Range          | -4° to 221°F (-20° to 105°C) |
| Operating Humidity Range           | 0% to 65% RH                 |
| Storage Humidity Range             | 0% to 65% RH                 |
| FEATURES & SPECIFICATIONS          |                              |
| Antibacterial                      | No                           |
| Angled Plug                        | No                           |
| High Voltage                       | Yes                          |
| Locking Plug                       | Yes                          |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Coiled Power Cord                   | No                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                     |
| Product Certifications              | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                  | RoHS; REACH                         |
| <b>WARRANTY &amp; SUPPORT</b>       |                                     |
| Product Warranty Period (Worldwide) | Lifetime limited warranty           |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.