

Not for use in European Markets

## Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13 - Green Dot, 10A, 125V, 18 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P006-L03-HG10



Connects a PC, printer, monitor, scanner or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

### Features

**Hospital-Grade Power Cable is a Safe Solution for Medical Facilities** This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible equipment with a three-pin C14 inlet in a hospital or other medical facility. It features a locking C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities. The three-foot length allows you flexibility in placing equipment with respect to the power outlet.

**Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C13 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

**Lifetime Warranty** The P006-L03-HG10 is backed by a lifetime warranty, ensuring reliability and performance.

## Specifications

| OVERVIEW             |  |
|----------------------|--|
| UPC Code             | 037332223142   |
| Device Compatibility | Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU |
| Country/Region       | North America  |

### Highlights

- Recommended for connecting devices to power outlets outside patient care vicinities
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Hospital-grade power cable replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

### Applications

- Connect a mobile cart battery, monitor, computer or printer to a hospital-grade surge protector up to 3 ft. away in a hospital environment outside patient care vicinities
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P006-L03-HG10 Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13, 3 ft., Black

| <b>INPUT</b>                         |                              |
|--------------------------------------|------------------------------|
| Maximum Input Amps                   | 10                           |
| Voltage Compatibility (VAC)          | 125                          |
| <b>PHYSICAL</b>                      |                              |
| Plug Color                           | Black                        |
| Cable Jacket Color                   | Black                        |
| Cable Jacket Material                | PVC                          |
| Cable Jacket Rating                  | VW-1                         |
| Power Cord Jacket Type               | SJT                          |
| Cable Outer Diameter (OD)            | 7.7mm                        |
| Number of Conductors                 | 3                            |
| Wire Gauge (AWG)                     | 18                           |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.82                         |
| Cable Length (ft.)                   | 3                            |
| Cable Length (m)                     | 0.91                         |
| Shipping Dimensions (hwd / in.)      | 10.00 x 7.09 x 0.50          |
| Shipping Dimensions (hwd / cm)       | 25.40 x 18.01 x 1.27         |
| Shipping Weight (lbs.)               | 0.37                         |
| Shipping Weight (kg)                 | 0.17                         |
| <b>ENVIRONMENTAL</b>                 |                              |
| Operating Temperature Range          | -4° to 221°F (-20° to 105°C) |
| Storage Temperature Range            | -4° to 221°F (-20° to 105°C) |
| Operating Humidity Range             | 0% to 65% RH                 |
| Storage Humidity Range               | 0% to 65% RH                 |
| <b>CONNECTIONS</b>                   |                              |
| Side A - Connector 1                 | NEMA 5-15P-HG                |
| Side B - Connector 1                 | IEC-320-C13 - LOCKING        |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                              |
| Antibacterial                        | No                           |
| Angled Plug                          | No                           |
| High Voltage                         | No                           |
| Locking Plug                         | Yes                          |

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Coiled Power Cord                   | No                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                     |
| Product Certifications              | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                  | RoHS; REACH                         |
| <b>WARRANTY &amp; SUPPORT</b>       |                                     |
| Product Warranty Period (Worldwide) | Lifetime limited warranty           |

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.