

## Power Cord Adapter, C14 to C5 - 7A, 125V, Black

MODEL NUMBER: P014-000



C14 to C5 adapter connects your notebook or laptop with a 3-slot C6 power connector to a C13 outlet on a surge protector or UPS.

### Features

**IEC C14 to IEC C5 Adapter Connects Notebook Computers to an AC Outlet** This UL-listed C14 to C5 power cord adapter converts a C6 plug into a C14 connector and is ideal for a device's built-in power cord that doesn't match an available outlet. You can use this adapter to connect a notebook computer, laptop or other device with a three-slot C6 power cord to a surge protector or UPS system with a C13 outlet.

### Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- Converts a C6 connector into a C14 connector to match an available outlet

### Applications

- Connect a laptop or notebook computer to a C13 outlet near your workstation
- Connect a laptop or notebook to a surge protector at a trade show or lecture hall

### Package Includes

- P014-000 IEC C14 to IEC C5 Power Cord Adapter, Black

## Specifications

OVERVIEW	
UPC Code	037332218001
Device Compatibility	Laptop; Computer; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	7
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C5
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Wire Gauge (AWG)	N/A
Wire Gauge (OD - mm <sup>2</sup> )	N/A
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	5.00 x 3.98 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.11 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	2.550 x 1.140 x 0.820
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	30% to 80% RH
Storage Humidity Range	30% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.