

## DVI-I Dual Link Digital and Analog Monitor Cable (DVI-I M/M), 15 ft. (4.57 m)

MODEL NUMBER: P560-015-DLI



### Description

This DVI-I Dual-Link Digital/Analog monitor cable delivers the high performance and high bandwidth needed for today's digital video displays. In addition, DVI-I transmits both digital and analog video signals, allowing this cable to be converted for use with a VGA monitor using a P126-000 adapter. Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Supports DVI Dual-Link video resolutions up to 2560 x 1600, and high-speed data transmission rates up to 9.9 Gbps. Both DVI-I connectors are molded and have integral strain relief for long life reliability. PC and macOS compatible. Meets DVI DDWG standards.

### Features

- DVI-I transmits both digital and analog video signals. Can be converted for use with a VGA monitor using a P126-000 adapter
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Gold plated contacts ensure excellent conductivity
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Supports DVI Dual Link video resolutions up to 2560 x 1600
- Supports high speed data transmission rates up to 9.9Gbps
- PC and Mac compatible
- Meets DVI DDWG standards

## Specifications

OVERVIEW	
UPC Code	037332185976
Product Type	Passive Cable
Technology	DVI
Cable Type	Passive

### Highlights

- DVI-I transmits both digital and analog video signals. Can be converted for use with a VGA monitor using a P126-000 adapter
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Gold plated contacts ensure excellent conductivity
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Supports DVI Dual Link video resolutions up to 2560 x 1600
- Supports high speed data transmission rates up to 9.9Gbps
- Meets DVI DDWG standards

### System Requirements

- DVI computer and monitor with DVI-I ports
- Can be converted for use with VGA monitors and/or computers using a P126-000 adapter
- In order to transmit from a DVI computer to a VGA monitor, the computer must support DVI-I Digital/Analog data transmission
- In order to achieve Dual Link video resolutions up to 2560 x 1600, your computer's video card and your monitor must also support Dual Link video resolutions

### Package Includes

- 15-ft. (4.57 m) DVI-I Dual Link Digital/Analog Monitor Cable



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	DVI-I DUAL LINK (MALE)
Side B - Connector 1	DVI-I DUAL LINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57
Cable Length (in.)	180
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Weight (lbs.)	1.08
Shipping Weight (kg)	0.49
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.