

# Laptop Power Cord Adapter, C14 to C5 - 2.5A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P014-02M-EU



Connects your notebook computer or laptop with a 3-slot C6 power inlet to a PDU or UPS system.

## Features

### Laptop Power Adapter Cord Connects Notebook Computers to an AC Outlet

This VDE-compliant power cable connects a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other power source with a C13 outlet. The P014-02M-EU features an IEC-320-C14 end for connecting to an AC power source and an IEC-320-C5 end for connecting to devices. The 6.6-foot (2-meter) cable allows you welcome flexibility in placing equipment with respect to the power outlet.

### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

## Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- 2-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable
- VDE-compliant H05VV-F jacket allows use in European IT applications

## Package Includes

P014-02M-EU C14 to C5 Laptop Power Cord Adapter, 2 m (6.6 ft.), Black

## Specifications

| OVERVIEW                    |                      |
|-----------------------------|----------------------|
| UPC Code                    | 037332280992         |
| Product Type                | Laptop Power Cord    |
| Device Compatibility        | Laptop; Monitor/HDTV |
| Country/Region              | Europe; UK           |
| INPUT                       |                      |
| Maximum Input Amps          | 2.5                  |
| Voltage Compatibility (VAC) | 250                  |
| CONNECTIONS                 |                      |
| Side A - Connector 1        | IEC-320-C14          |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                               |
|--------------------------------------|-------------------------------|
| Side B - Connector 1                 | IEC-320-C5                    |
| <b>PHYSICAL</b>                      |                               |
| Plug Color                           | Black                         |
| Cable Jacket Color                   | Black                         |
| Cable Jacket Material                | PVC                           |
| Power Cord Jacket Type               | H05VV-F                       |
| Cable Outer Diameter (OD)            | 6.7 mm                        |
| Number of Conductors                 | 3                             |
| Conductor Gauge                      | 24/0.20AS                     |
| Wire Gauge (AWG)                     | 18                            |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.75                          |
| Power Cord Color                     | Black                         |
| Cable Length (ft.)                   | 6.56                          |
| Cable Length (m)                     | 2.00                          |
| Shipping Dimensions (hwd / in.)      | 9.02 x 7.01 x 0.50            |
| Shipping Dimensions (hwd / cm)       | 22.91 x 17.81 x 1.27          |
| Shipping Weight (lbs.)               | 0.38                          |
| Shipping Weight (kg)                 | 0.17                          |
| Unit Dimensions (hwd / in.)          | 9.020 x 7.010 x 0.500         |
| Unit Packaging Type                  | Polybag                       |
| Unit Weight (lbs.)                   | 0.36                          |
| Unit Weight (kg)                     | 0.16                          |
| <b>ENVIRONMENTAL</b>                 |                               |
| Operating Temperature Range          | 5° to 158° F (-15° to 70° C)  |
| Storage Temperature Range            | 5° to 140° F (-15° to 60° C)  |
| Relative Humidity                    | 10 ~ 65% RH, Non-Condensing   |
| Operating Humidity Range             | 20% TO 80% RH, NON-CONDENSING |
| Storage Humidity Range               | 20% TO 80% RH, NON-CONDENSING |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                               |
| Antibacterial                        | No                            |
| Armored Cable                        | No                            |
| Angled Plug                          | No                            |
| High Voltage                         | Yes                           |
| Locking Plug                         | No                            |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                |
|-------------------------------------|--------------------------------|
| Coiled Power Cord                   | No                             |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                |
| Product Compliance                  | CE (Europe); REACH; RoHS; UKCA |
| <b>WARRANTY &amp; SUPPORT</b>       |                                |
| Product Warranty Period (Worldwide) | Lifetime limited warranty      |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.