

## Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 2 ft. (0.61 m), White

MODEL NUMBER: P018-002-AWH



Heavy-duty C14 to C15 power cord connects a PoE network switch or other device with a C16 power inlet to a PDU or UPS system.

### Features

**C15 to C14 Power Cord for Network Devices That Require a Heavy-Gauge Connection** This 250V C15 to C14 cable features 14 AWG wire suitable for high power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as electric kettles, PoE (Power over Ethernet) switches with high-wattage power supplies, and similar network components. This IEC C14 to IEC C15 cord can also replace or upgrade the standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime** This C15 to C14 power cable features a white SJT jacket and fully molded white ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

## Specifications

| OVERVIEW                    |                          |
|-----------------------------|--------------------------|
| UPC Code                    | 037332199096             |
| Device Compatibility        | Network Switch; UPS; PDU |
| Country/Region              | North America            |
| INPUT                       |                          |
| Maximum Input Amps          | 15                       |
| Voltage Compatibility (VAC) | 100-250                  |

### Highlights

- Recommended for powering PoE switches with high-wattage power supplies
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- C14 to C15 power cable replaces or upgrades original manufacturer's power cord
- Color-coded white for fast, easy identification in a crowded rack or workstation
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like high-wattage PoE switches to a PDU up to 2-ft. (0.61 m) away in your data center
- Update or replace the standard power cord provided by a device's original manufacturer
- Extend an existing power connection by 2-ft. (0.61 m)

### Package Includes

- P018-002-AWH IEC C14 to IEC C15 Power Cable, 2-ft. (0.61 m), White

| <b>PHYSICAL</b>                      |                             |
|--------------------------------------|-----------------------------|
| Plug Color                           | White                       |
| Cable Jacket Color                   | White                       |
| Cable Jacket Material                | PVC                         |
| Cable Jacket Rating                  | FT2                         |
| Power Cord Jacket Type               | SJT                         |
| Cable Outer Diameter (OD)            | 9.2mm                       |
| Number of Conductors                 | 3                           |
| Wire Gauge (AWG)                     | 14                          |
| Wire Gauge (OD - mm <sup>2</sup> )   | 2.08                        |
| Cable Length (ft.)                   | 2                           |
| Cable Length (m)                     | 0.61                        |
| Cable Length (cm)                    | 60.96                       |
| Shipping Dimensions (hwd / in.)      | 9.90 x 7.00 x 0.50          |
| Shipping Dimensions (hwd / cm)       | 25.15 x 17.78 x 1.27        |
| Shipping Weight (lbs.)               | 0.33                        |
| Shipping Weight (kg)                 | 0.15                        |
| <b>ENVIRONMENTAL</b>                 |                             |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range             | 20% to 80% RH               |
| Storage Humidity Range               | 20% to 80% RH               |
| <b>CONNECTIONS</b>                   |                             |
| Side A - Connector 1                 | IEC-320-C14                 |
| Side B - Connector 1                 | IEC-320-C15                 |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                             |
| Antibacterial                        | No                          |
| Angled Plug                          | No                          |
| High Voltage                         | Yes                         |
| Locking Plug                         | No                          |
| Coiled Power Cord                    | No                          |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                             |

|                                     |                           |
|-------------------------------------|---------------------------|
| Product Certifications              | cUL Listed; UL Listed     |
| Product Compliance                  | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |