

Active High-Speed HDMI Cable with Built-In Signal Booster (M/M), Black, 80 ft. (24.38 m)

MODEL NUMBER: P568-080-ACT



High-speed long-range premium cable connects two HDMI devices up to 80 ft. apart. Built-in signal booster avoids the expense and effort of connecting a repeater between two separate HDMI cables.

Description

The P568-080-ACT Active High-Speed HDMI Cable (M/M) connects a computer, cable box or Blu-ray™ source to a high-definition monitor, projector or television up to 80-ft. (24.38 m) away. Its built-in signal booster allows a clean audio/video transmission without the effort and expense of adding an external repeater to your HDMI cable run. Plus, a built-in equalization control lets you manually adjust the display image to your liking.

The P568-080-ACT is recommended for digital signage, boardroom and classroom presentations, point-of-sale displays, businesses and other applications that display HD video and multi-channel audio. It supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz. When used with an Apple® digital A/V adapter, it supports iPad2® video mirroring for playing games, watching videos or displaying presentations. Backward compatible with previous HDMI generations, the P568-080-ACT is compliant with HDCP v1.3 standards.

The 80-ft. (24.38 m) molded 28 AWG cable features foil and braid shielding to deliver top-of-the-line signal quality and protection from crosstalk and EMI/RFI interference. Corrosion-resistant gold-plated connectors and contacts provide maximum conductivity and minimize data loss. Integral strain relief with ridges on each end gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. A flexible PVC jacket makes the cable easy to install in tight spaces.

Features

Connects HDMI Source to High-Definition TV, Projector or Monitor

- Recommended for digital signage, boardroom and classroom presentations, point-of-sale displays, businesses and other applications that display HD video and multi-channel audio

Highlights

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Signal booster allows clean signal transmission up to 80-ft. (24.38 m)
- Built-in equalization control allows manual image adjustment
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated connectors for optimal signal transfer

Package Includes

- P568-080-ACT Active High-Speed HDMI Cable with Built-In Signal Booster (M/M), Black, 80 ft.
- HDMI power adapter cable



Built-In Signal Booster for Long-Range Cable Needs

- Allows a clear A/V transmission up to 80 ft.
- Eliminates expense and effort of adding external repeater to cable run
- Equalization control allows manual adjustment of display image

High Performance and Wide Compatibility

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports iPad2 video mirroring when used with Apple digital A/V adapter
- Backward compatible with previous HDMI generations
- Complies with HDCP v1.3 standards

Superior Quality Ensures a Flawless Signal

- Corrosion-resistant gold-plated black connectors for optimal signal transfer
- Fully molded 28 AWG construction with integral strain relief for durability and long life
- Premium foil and braid shielding for EMI/RFI noise protection
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332200679
Product Type	Active Cable
Technology	HDMI
Form Factor and Mounting Options	Cable
VIDEO	
Video Input	HDMI (MALE)
Video Output	HDMI (MALE)
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	80
Max 1920 x 1080 (1080p) Range (ft)	80
Signal Range (ft.)	80
Signal Range (m)	24.4
AUDIO	
Audio Input	HDMI
Audio Output	HDMI



Audio Specification	Stereo Audio
INPUT	
Cable Length (ft.)	80
Cable Length (m)	24.4
POWER	
Power Source	Receiver end only (Optional)
Power Source Type	USB
PHYSICAL	
Color	Black
Number of Displays	1
Shipping Dimensions (hwd / cm)	1.27 x 30.48 x 31.75
Shipping Dimensions (hwd / in.)	0.50 x 12.00 x 12.50
Shipping Weight (kg)	1.91
Shipping Weight (lbs.)	4.20
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 158°F (0 to 70°C)
Storage Temperature Range	14 to 176°F (-10 to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
FEATURES & SPECIFICATIONS	
HDMI Specification	1.3



HDCP Specification	1.3
Driver Required	No
Built-In Equalizer	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>