

Power Extension Cord, C20 to C19 - Heavy-Duty, 20A, 250V, 12 AWG, 2 ft. (0.6 m), Blue

MODEL NUMBER: P036-002-ABL



C19 to C20 20A heavy-duty extension cable connects high-output devices with C19/C20 power connectors, including blade server chassis.

Features

20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection

This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The two-foot (0.6-meter) length helps reduce cable clutter and minimize the risk of tripping.

Blue Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The UL-listed cable has a blue PVC jacket, which is easy to identify quickly in a crowded PDU or UPS system and helps prevent the cable from becoming accidentally disconnected.

Highlights

- Recommended for powering servers, routers and other high-output network devices
- Blue cable jacket allows quick identification of devices in a crowded rack enclosure
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

Package Includes

P036-002-ABL C19 to C20 Heavy-Duty Extension Cord, 2 ft. (0.6 m), Blue

Specifications

| OVERVIEW | |
|-----------------------------|--|
| UPC Code | 037332289001 |
| Device Compatibility | Network Switch; PDU; Router; Server; UPS |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 20 |
| Voltage Compatibility (VAC) | 250 |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C20 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|-------------------------------|
| Side B - Connector 1 | IEC-320-C19 |
| PHYSICAL | |
| Plug Color | Blue |
| Cable Jacket Color | Blue |
| Connector Color | Blue |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 8.2mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 12 |
| Wire Gauge (OD - mm ²) | 1.5 |
| Cable Length (ft.) | 2 |
| Cable Length (m) | 0.61 |
| Cable Length (in.) | 24 |
| Shipping Dimensions (hwd / in.) | 10.00 x 7.99 x 0.50 |
| Shipping Dimensions (hwd / cm) | 25.40 x 20.29 x 1.27 |
| Shipping Weight (lbs.) | 0.93 |
| Shipping Weight (kg) | 0.42 |
| Unit Dimensions (hwd / in.) | 10.000 x 7.990 x 0.500 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Relative Humidity | 10% to 65% RH |
| Operating Humidity Range | 20% TO 80% RH, NON-CONDENSING |
| Storage Humidity Range | 20% TO 80% RH, NON-CONDENSING |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | No |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Product Certifications | UL Listed |
| Product Compliance | WEEE |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.