

Not for use in European Markets

Power Extension Cord, Locking C19 to C20 - Heavy-Duty, 20A, 100-250V, 12 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P036-L06



C20 to C19 cord powers a server, router, switch, blade server enclosure or other network device that requires a heavy-gauge cable.

Features

C20 to C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection This rugged cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a server, router, switch, blade server enclosure or other network device to a UPS system or PDU. It is also an ideal replacement or upgrade from the standard power cord provided by the device's manufacturer. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Locking C19 Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C19 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Lifetime Warranty The P036-L06 is backed by a lifetime warranty, ensuring reliability and performance.

Specifications

| OVERVIEW | |
|----------------------|--|
| UPC Code | 037332218315 |
| Device Compatibility | Server; Router; Network Switch; UPS; PDU |
| Country/Region | North America |
| INPUT | |

Highlights

- Recommended for powering network devices that require heavy-gauge cabling
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Reliable replacement or upgrade from standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking C19 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like servers, routers and network switches to a UPS system up to 6-ft. (1.83 m) away in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P036-L06 C20 to C19 Power Cable, Locking C19 Connector, 6-ft. (1.83 m), Black

| | |
|--------------------------------------|------------------------------|
| Maximum Input Amps | 20 |
| Voltage Compatibility (VAC) | 100-250 |
| PHYSICAL | |
| Plug Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 10.8mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 12 |
| Wire Gauge (OD - mm ²) | 3.31 |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 12.80 x 8.59 x 0.50 |
| Shipping Dimensions (hwd / cm) | 32.51 x 21.82 x 1.27 |
| Shipping Weight (lbs.) | 0.98 |
| Shipping Weight (kg) | 0.44 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 221°F (-20° to 105°C) |
| Storage Temperature Range | -4° to 221°F (-20° to 105°C) |
| Operating Humidity Range | 0% to 65% RH |
| Storage Humidity Range | 0% to 65% RH |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C20 |
| Side B - Connector 1 | IEC-320-C19 - LOCKING |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | Yes |
| Coiled Power Cord | No |

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

| STANDARDS & COMPLIANCE | |
|-------------------------------------|-------------------------------------|
| Product Certifications | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.