


## Power Cord, C14 to C21 - Heavy-Duty, 15A, 250V, 14 AWG, 3 ft. (0.9 m), Red

MODEL NUMBER: P037-003-ARD



C14 to C21 15A heavy-duty cable connects high-output devices with C13/C22 power connectors commonly found on high-powered IT equipment.

### Features

#### 15A C14-to-C21 Power Cable for Network Devices That Require a Heavy-Gauge Connection

This heavy-duty cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable, including AI/machine-learning data centers. The three-foot (0.9-meter) length helps reduce cable clutter by providing a tailor-made fit between the device and the PDU or UPS in a crowded rack enclosure.

#### Recommended for High-Temperature Environments

The P037-003-ARD can be used to connect a blade server, large router or network switch with a C22 inlet, usually found on high-powered, high-temperature (overall operating temperature maximum 105°C/221°F) equipment, to a PDU or UPS system. It's an ideal upgrade to a power cord with improved temperature threshold for data center applications in which temperature control and fire safety are high priorities.

#### Red Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The UL-listed cable has a red PVC jacket with fully molded red ends, which is easy to identify quickly in a crowded PDU or UPS system and helps prevent the cable from becoming accidentally disconnected.

### Highlights

- Recommended for powering switches, servers and other high-powered network devices
- 15A C21/C14 connectors support temperatures up to 221°F (105°C) frequent in rack enclosures
- Thick 14 AWG wire manages high power levels required for larger equipment
- 3 ft. length allows flexibility in mounting devices in a rack while avoiding cable clutter
- Red cable jacket allows quick identification of devices in a crowded rack enclosure

### Package Includes

P037-003-ARD Power Cord, C14 to C21, 3 ft. (0.9 m), Red

## Specifications

| OVERVIEW             |                            |
|----------------------|----------------------------|
| UPC Code             | 037332293299               |
| Device Compatibility | Computer; Server; UPS; PDU |
| Country/Region       | North America              |
| INPUT                |                            |
| Maximum Input Amps   | 15                         |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                               |
|--------------------------------------|-------------------------------|
| Voltage Compatibility (VAC)          | 250                           |
| <b>CONNECTIONS</b>                   |                               |
| Side A - Connector 1                 | IEC-320-C14                   |
| Side B - Connector 1                 | IEC-320-C21                   |
| <b>PHYSICAL</b>                      |                               |
| Plug Color                           | Red                           |
| Cable Jacket Color                   | Red                           |
| Cable Jacket Material                | PVC                           |
| Cable Jacket Rating                  | FT2; VW-1                     |
| Power Cord Jacket Type               | SJT                           |
| Cable Outer Diameter (OD)            | 11mm                          |
| Number of Conductors                 | 3                             |
| Wire Gauge (AWG)                     | 12                            |
| Wire Gauge (OD - mm <sup>2</sup> )   | 3.31                          |
| Cable Length (ft.)                   | 3                             |
| Cable Length (m)                     | 0.91                          |
| Cable Length (in.)                   | 36                            |
| Shipping Dimensions (hwd / in.)      | 12.80 x 8.86 x 0.50           |
| Shipping Dimensions (hwd / cm)       | 32.51 x 22.50 x 1.27          |
| Shipping Weight (lbs.)               | 0.62                          |
| Shipping Weight (kg)                 | 0.28                          |
| Unit Dimensions (hwd / in.)          | 12.800 x 8.900 x 0.500        |
| <b>ENVIRONMENTAL</b>                 |                               |
| Operating Temperature Range          | -4° to 221°F (-20° to 105°C)  |
| Storage Temperature Range            | -4° to 221°F (-20° to 105°C)  |
| Operating Humidity Range             | 10% TO 65% RH, NON-CONDENSING |
| Storage Humidity Range               | 10% TO 65% RH, NON-CONDENSING |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                               |
| Antibacterial                        | No                            |
| Angled Plug                          | No                            |
| High Voltage                         | Yes                           |
| Locking Plug                         | No                            |
| Coiled Power Cord                    | No                            |



Powering Business Worldwide

TRIPP LITE  
SERIES

| STANDARDS & COMPLIANCE              |                           |
|-------------------------------------|---------------------------|
| Product Certifications              | cUL Listed; UL Listed     |
| Product Compliance                  | WEEE                      |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.